

CONUS cable gland


63xxMxxPA

Configuration

Pressure screw	Polyamide PA6 GF30
Washer	Polyethylene PE-LD
Sealing ring	SBR/NBR
Gland body	Polyamide PA6 GF30
Connecting thread	metric, as per EN 60423

Properties

	for application in installation sectors without special requirements
Temperature range	-30°C +80°C
Protection grade	IP55



Features



RAL 7035

Connecting thread standard length

A	ØC	L	SW1	SW2	H		Part No.
	mm	mm	mm	mm	mm	Piece	
M12x1,5	6 - 8	11	19	16	33	50	6309M12PA
M16x1,5	6 - 8	11	19	16	34	50	6309M16PA
M20x1,5	8 - 10	11	22	19	36	50	6311M20PA
M20x1,5	10 - 12	11	24	21	36	50	6313M20PA
M20x1,5	12 - 14	11	27	23	38,5	50	6316M20PA
M25x1,5	12 - 14	11	27	23	40	50	6316M25PA
M25x1,5	15 - 17	11	32	30	43	50	6321M25PA
M32x1,5	15 - 17	10	36	30	38	25	6321M32PA
M32x1,5	24 - 26	11	42	40	46,5	25	6329M32PA
M40x1,5	24 - 26	11	42	40	45,5	10	6329M40PA
M50x1,5	31 - 33	11	53	50	52	10	6336M50PA
M50x1,5	38 - 40	11	60	55	57,5	10	6342M50PA

A	ØC	L	SW1	SW2	H		Part No.
	mm	mm	mm	mm	mm	Piece	
M63x1,5	43 - 44	11	65	60	57,5	10	6348M63PA

From part no. 6342M50PA without glass fibre reinforcement