





| REV. | DATE     | ECR NO. | DESCRIPTION     |
|------|----------|---------|-----------------|
| NC   | 07/02/10 | XXXXXX  | INITIAL RELEASE |



RECOMMENDED  
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE  
HEX CRIMP SIZE .324"
2. CRIMPED CONTACT PIN  
HEX CRIMP SIZE .068"

|    |               |          |         |     |
|----|---------------|----------|---------|-----|
| 10 | FERRULE       | BRASS    | NICKEL  | 1   |
| 9  | CONTACT PIN   | BRASS    | GOLD    | 1   |
| 8  | WASHER        | BRASS    | NICKEL  | 1   |
| 7  | SPRING        | SK5      | NICKEL  | 1   |
| 6  | RETAINER RING | BRASS    | NICKEL  | 1   |
| 5  | GASKET        | RUBBER   | RED     | 1   |
| 4  | BARREL        | BRASS    | NICKEL  | 1   |
| 3  | INSULATOR     | PTFE     | NATURAL | 1   |
| 2  | SHELL         | BRASS    | NICKEL  | 1   |
| 1  | BODY          | BRASS    | NICKEL  | 1   |
|    | DESCRIPTION   | MATERIAL | FINISH  | QTY |

|                                                                                                                                        |
|----------------------------------------------------------------------------------------------------------------------------------------|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.             |
| UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br>0.5 – 8mm ± 0.20mm<br>8 – 30mm ± 0.40mm<br>30 – 120mm ± 0.50mm           |
| UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br>.020 – .315 = ± 0.007"<br>.315 – 1.180 = ± 0.015"<br>1.180 – 4.724 = ± 0.020" |
| DO NOT SCALE DRAWING                                                                                                                   |

| APPROVALS     | DATE                 |
|---------------|----------------------|
| DRAWN M.ZHANG | 07/02/10             |
| CHECKED       |                      |
| ISSUED        |                      |
| SHEET 1 OF 1  |                      |
| CAD FILE      | C:/CONNEX/112981.DWG |

|                                                                |            |       |    |
|----------------------------------------------------------------|------------|-------|----|
| <div>Amphenol Connex</div>                                     |            |       |    |
| PART DESCRIPTION                                               |            |       |    |
| BNC CRIMP PLUG (FOR BELDEN 1794A, 7855A, GEPCO VHD 7000 CABLE) |            |       |    |
| PART NO.                                                       |            |       |    |
| 112981                                                         |            |       |    |
| DWG. NO.                                                       | 112981.DWG | REV.  | NC |
| SIZE                                                           | A          | SCALE | NA |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112981](#)