



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT
DPA24688TGY	1.26 lb (572.73 g)

## NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
2. MATERIAL:  
PANEL HOUSING: STEEL  
RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0  
PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0  
BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B  
RETENTION CAP:  
THERMOPLASTIC RESIN UL94V-0
3. 24 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
4. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
5. FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6x1x15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
6. DIMENSIONS IN BRACKETS ARE IN METRIC.
7. USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
8. RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



CID\*\*-C & CIP\*\*-C, PHONE OR DATA ICON LOCATES HERE. IDENTIFIES INDIVIDUAL PORT. OPTIONAL, NOT SUPPLIED.

PART NUMBER		DPA24688TGY	
TITLE			
DP6 PLUS 24 PORT ANGLED PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479JD/04	
DATASET FILE NAME		M02479JD_DC240/00C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ± .03 [.8]		SEE NOTE 2	
.XXX ± .010 [.3]		DRAWING NUMBER:	
ANGLES ±		02479-240	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
LZ	3-04-06	CEF	.25-1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	5-30-14	MDJR	REFR	MMR	A. UPDATED TITLE BLOCK. ALL PREVIOUS REVISIONS HAVE BEEN REMOVED FOR CLARITY.	02479-240