

**LIFETIME
WARRANTY**

Fig. 1



Fig. 2




Fig. 3





Fig. 4


F & LARGE O.D. CRIMPER

ITEM #	DESCRIPTION	FIG.
TFC-4000	F STANDARD CRIMPER FOR RG59/62, 6 WITH HEX CRIMP. FEATURES PARALLEL ACTION AND NICKEL PLATED SURFACES	1
TFC-4010	F PRO CRIMPER FOR RG59/62/6 WITH TENSION ADJUSTMENT- HEX SIZES .255", .322"	2
TFC-4020	LARGE O.D. PRO CRIMPER FOR RG8/11/213 WITH TENSION ADJUSTMENT HEX SIZES .100", .322", .448"	3
TFC-4030	LARGE O.D. PRO CRIMPER FOR RG6/8/11 WITH TENSION ADJUSTMENT HEX SIZES .100", .359", .406"	3
TFC-4035	LARGE O.D. PROFESSIONAL CRIMPER FOR RG-11/ RG-6 QUAD F CONNECTORS. HEX SIZES .096", .410", .475"	3

D-SUB CONTACT CRIMPER

ITEM #	DESCRIPTION	FIG.
TFC-5000	NON-RATCHET CRIMP TOOL FOR OPEN BARREL D-SUB CONTACTS 20 22/24-26/28 AWG WITH CUTTER	4
TRF-4000	RATCHET PRO-GRADE CONTACT CRIMPER FOR D-SUB MINIATURE OPEN BARREL CONTACTS, V35 CONTACTS AND NON-INSULATED PINS 18-22/24-30 AWG WITH TENSION ADJUSTMENT	5
TFC-6000	4-WAY INDENT D-SUB MACHINED CONTACT CRIMP TOOL	6

Fig. 5



Fig. 6

