

F

E

D

C

B

A

F




E

D

C


B

A




30.5	29.3	25.65	24.5	54132-5031	50
28.0	26.8	23.15	22.0	-4531	45
27.0	25.8	22.15	21.0	-4331	43
25.5	24.3	20.65	19.5	-4031	40
24.5	23.3	19.65	18.5	-3831	38
23.5	22.3	18.65	17.5	-3631	36
23.0	21.8	18.15	17.0	-3531	35
22.5	21.3	17.65	16.5	-3431	34
22.0	20.8	17.15	16.0	-3331	33
21.5	20.3	16.65	15.5	-3231	32
20.5	19.3	15.65	14.5	54132-3031	30
D	C	B	A	MATERIAL NO.	CKT.

REVISED EC NO: J2006-2797 DRAWN: NABE1 CHKD: KTOYODA APPR: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	±0.2	DRAWN BY K. KOHAMA	DATE '00/09/13	TITLE 0.5 FPC CONN. ZIF HOUSING ASSY FOR SMT. (R/A) BOTTOM CONTACT			
		10 OVER 30 UNDER	±0.25	CHECKED BY S. KUNISHI	DATE '00/09/13				
		30 OVER	±0.3	APPROVED BY M. FUKUSHIMA	DATE '00/09/13				 MOLEX INCORPORATED
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.			
	A	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3 SEE CHART		SD-54132-011		1 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									





EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	REVISED EC NO. JC2001-0487 DRWN: K.KOHAMA '00/02 CHK: S.KUNISHI '00/02 APPR: M.FUKUSHIMA '00/02	RELEASED EC NO. JC2001-0171 DRWN: K.KOHAMA '00/09/0 CHK: S.KUNISHI '00/09/0 APPR: M.FUKUSHIMA '00/09/0	REV
A					

DETAIL "F"




引き出し方向
PULL OUT
DIRECTION




NOTES

- 梱包数量：1500個／リール
NUMBER OF CONNECTORS：1500PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- トップテープの剥離強度：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED , DURING TRANSPORTATION.



- 材料
キャリアテープ：ポリプロピレン (PP)
トップテープ：PET, PE, PEF
リール：ポリスチレン (PS) <リサイクル材を含む>

MATERIAL CARRIER TAPE:POLYPROPYLENE
TOP TAPE:PET,PE,PEF
REEL:POLYSTYREN(PS)
<RECYCLE MATERIAL CONTAINED>

MATERIAL 材料	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE 2:1	DESIGN UNITS ☒ mm ☐ INCH	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY	SHT REVISE ON CAD ONLY
FINISH 仕上げ	10 UNDER 未満	±0.2	DRAWN BY & DATE K.KOHAMA '00/09/13	TITLE: EMBOSSD TAPE PACKAGE FOR 0.5 FPC CONN. ZIF	
WIRE RANGE 適用電線範囲	10 OVER 30 UNDER 以上 未満	±0.25	CHECKED BY & DATE S.KUNISHI '00/12/22	MATERIAL NO. 54132012.S01	
INS. RANGE 被覆外径	30 OVER 以上	±0.3	APPROVED BY & DATE M.FUKUSHIMA '00/12/22	DRAWING NO. SD-54132-012	
	ANGLE 角度	±3°	CAD FILENAME 54132012.S01	SHEET NO. 1 OF 2	
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		

DWG. NO.
SD-54132-012

E

D

A

C

B

DO NOT SCALE DRAWING

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	REVISED EC NO. JC2001-0487 DRWN: K.KOHAMA '00/02/22 CHK: S.KUNISHI '00/02/22 APPR: M.FUKUSHIMA '00/02/22	RELEASED EC NO. JC2001-0171 DRWN: K.KOHAMA '00/09/03 CHK: S.KUNISHI '00/09/03 APPR: M.FUKUSHIMA '00/09/03	REV
A			O		
			DESCRIPTION		
			MATERIAL		
			FINISH		
			WIRE RANGE		
			INS. RANGE		

SHEET 1 OF 2 参照
REFER TO SHEET 1 OF 2

WIRE RANGE
適用電線範囲

INS. RANGE
被覆外径

GENERAL TOLERANCES:
(UNLESS SPECIFIED)
一般公差

10 UNDER 未満	±0.2
10 OVER 以上	±0.25
30 OVER 以上	±0.3
ANGLE 角度	±3°

SCALE
2:1

DESIGN UNITS
☒ mm ☐ INCH

DRAWN BY & DATE
K.KOHAMA '00/09/13

CHECKED BY & DATE
S.KUNISHI '00/12/22

APPROVED BY & DATE
M.FUKUSHIMA '00/12/22

CAD FILENAME
54132012.S02

DIMENSIONS:
☐ mm ☐ INCH ☒ mm ONLY

THIRD ANGLE
PROJECTION

TITLE:
EMBOSSD TAPE PACKAGE
FOR 0.5 FPC CONN. ZIF

MOLEX INCORPORATED




MATERIAL NO.
54132-***92

DRAWING NO.
SD-54132-012

SHEET NO.
2 OF 2

SIZE
B

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.



44	45.5	30.8	31.6	26.1	29.6	54132-5092	50
		28.3	29.4	23.6	27.1	-4592	45
		27.3	28.4	22.6	26.1	-4392	43
		25.8	26.9	21.1	24.6	-4092	40
		24.8	25.9	20.1	23.6	-3892	38
		23.8	24.9	19.1	22.6	-3692	36
		23.3	24.4	18.6	22.1	-3592	35
		22.8	23.9	18.1	21.6	-3492	34
		22.3	23.4	17.6	21.1	-3392	33
		21.8	22.9	17.1	20.6	-3292	32
		20.8	21.9	16.1	19.6	54132-3092	30
キャリアテープ幅 CARRIER TAPE WIDTH	E	D	C	B	A	ENG. NO.	CKT.

8

7

6

5

4

3

2

EN-02J(097) MXJ-54