


Feature -


 6A, 30VDC for power
 SPST, lock / non-lock function

Application -

 home electronic equipments
 industrial electronic equipments
 audio system
 ADSL modem
 wireless AP



SPECIFICATIONS

SWITCH SPECIFICATIONS	
POLE - POSITION	Lock type are Available
CONTACT RATING	30 V DC , 6 A ; 30 V DC , 2 A
CONTACT RESISTANCE	100 mΩ MAX. 1.5 V DC ; 100 mA , by method of voltage DROP
INSULATION RESISTANCE	100 MΩ MIN. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not allowable ; 500 V AC for 1 minute
OPERATING FORCE	300 ± 150 gf
OPERATING LIFE	6,000 cycles
OPERATING TEMPERATURE RANGE	-20°C ~ 70°C
TOTAL TRAVEL	3.8 ± 0.3 mm


HOW TO ORDER


► DIMENSION


PS015-PLAA



► SCHEMATIC



► P.C.B LAYOUT



► MATERIAL

- ACTUATOR : PA66
- FRAME : STEEL PLATE , TIN PLATING
- TERMINAL : BRONZE SILVER PLATING
- SPRING : STAINLESS STEEL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[PS015-PLAA](#) [PS015-PLAA-2](#)