


MATERIAL

Insulator : PBT+30% Glass fiber

Contact Pin : Brass

SPECIFICATION

Current Rate : 1 AMP

Insulation Resistance : 5000MΩMin. at DC 500V

Contact Resistance : 20mΩMax. at DC 100mA

Dielectric Voltage : 500V AC for one minute

Operation Temperature : -55°C to +105°C

RoHS
Compliant

HSM 玄茂科技股份有限公司

HSUAN MAO TECHNOLOGY CO., LTD.

APPD.
核准

DWG.
製圖

ELAINE

DATA 製表日

2008/11/17



SCALE
比例

參考

UNIT
單位

M M

PAGE
張數

1 OF 1



TOLERANCE
容許公差

0 ±

.00 ±

ANG. ±

SIZE
紙張尺寸

A 4

REV.
版次

A

PART NAME 品名 2.54mm MINI

JUMPER 2P H:6.0mm OPEN COVER

GOLD PLATING BLUE COLOR

PART NO.

料號 C2700-02AAGL00R