


# 2.5mm Stereo Jack

161-3304-E



2.5mm Stereo Jack



Dimensions: mm (IN.)

SPECIFICATIONS	
<b>Housing:</b>	LCP black UL94V-0
<b>Terminals:</b>	Phosphor bronze silver plated
<b>Tip terminals:</b>	Cu alloy silver plated
<b>Insertion/ Ext. force:</b>	.3-3 Kgs
<b>Dielectric strength:</b>	250 VAC for 1 min.
<b>Insulation resistance:</b>	100 M ohm minimum
<b>Contact resistance:</b>	50 m ohm maximum
<b>Life cycle:</b>	5000 mating minimum
<b>Operating temperature:</b>	-25°C to +85°C
<b>Voltage rating:</b>	16.0 VDC
<b>Current Rating:</b>	0.3 A
RoHS Compliant	

Date Last Revised: 6-13-06

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC- 300980

161-3304-E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3304-E](#)