




FEATURES:

- Interface telecom DS0 signals to various test instruments
- Provides quick access between double banana jacks and 3 conductor phone jacks
- Double banana Plug is molded directly to the cable for added pull strength

MATERIALS:

WE-310 Plug: Brass, Unplated

Spring: Beryllium Copper, Nickel plated

Plug Body: Brass

Cable Type: 2 Conductor Shielded Microphone, .180" O.D.

RATINGS:

Operating Voltage: 300 VRMS

Operating Temperature: +55°C (+131°F) Max.

ORDERING INFORMATION: Model 6524-96

Standard Length = 96" (243 cm)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90967 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com