


Capacitor, film, 0.15 uF, +/-20% Tol, -40/+110C, Safety: X2, 275VAC,
 Lead Spacing=15 mm



Dimensions (mm)

| ID | Dimension | Tolerance |
|----|-----------|-----------|
| L | 18 | +0.3 |
| H | 12 | +0.1 |
| T | 6 | +0.2 |
| S | 15 | |
| LL | 4 | +2 |
| F | 0.6 | +/-0.05 |

Specifications

| | |
|-----------------------------|-------------|
| Manufacturer: | KEMET |
| Brand: | Arcotronics |
| Capacitance: | 0.15 uF |
| Temperature Range: | -40/+110C |
| Rated Temperature: | 105C |
| Voltage @ rated temp: | 560V |
| Voltage AC: | 275VAC |
| Tolerance: | +/-20% |
| Body Type: | Radial Box |
| Construction: | Wound |
| Application: | Safety: X2 |
| Dissipation Factor @ 1 kHz: | 0.1% |
| Insulation Resistance: | 100 GOhm |
| Maximum dVdT: | 400V/us |
| UL_1414: | 250V |
| UL_1283: | 310V |
| IEC_60384-14: | 275V |
| CSA_384-14: | 275V |
| CQC_GBT 14472: | 275V |
| Package Kind: | Bulk |
| Package Type: | Bag |
| Package Quantity: | 1750 |