

Item # ATV12HU22M3, Variable Speed Drive



Variable Speed Drive

Variable Speed Drive

SPECIFICATIONS

Family	Altivar 12
Product Line	AC Drives
Output Ampere Rating	10
Application	Variable &Constant
Enclosure Rating	IP20
Frame Size	B
HP Rating	3
kW Rating	2.2
Voltage Rating	230/230VAC
Input Phase	3 Phase
Output Phase	3 Phase
Control Voltage	24Vdc
Logic Input	4
Analog Input	1

Analog Output	1
Logic/Relay Outputs	1 protected relay output, 1 N/O contact and 1 N/C
Weight [lb]	2.64
Weight [kg]	1.20
UL File No.	E116875
CSA File	2159172
Other	CE, GOST, RoHS, NOM, EMITECH,UL
Communication	Modbus

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV12HU22M3](#)