


DC Power Plugs



171-3219, 171-3220

KOBI CONN


DC Power Plugs



171-3219



171-3220



Dimensions: In.

SPECIFICATIONS	
Color:	Black
Cap:	PP
Insulator A:	POM
Insulator B:	PC
Contact & Sleeve:	Nickel Plated Brass
Terminals:	Solder, Nickel Plated Brass
Insulation Resistance:	100MΩ (min.) @ 500VDC
Dielectric Strength:	500VAC for 1 minute
Voltage Ratings:	171-3219: 3.15V-6.3VDC
	171-3220: 6.3V-10.5VDC
Current Rating:	2A
Mating Jacks:	171-3219: 163-4310
	171-3220: 163-4311

Date Last Revised: 6/21/12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300035

171-3219, 171-3220

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3219](#) [171-3220](#)