





PRODUCT NUMBER	PITCH
0Qxx54x000J0G	5.08 mm




RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item ① Male contact pin: Copper Tin plated
- Item ② Terminal housing: Thermoplastic (UL94V-0)

- Electrical:
- Voltage rating: 300V/300V/300V
 - Current rating: 20A/20A/20A
 - Withstanding Voltage: 1.6 KV/2.5KV/2.5KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval: cULus /VDE /TUV



DIMENSION

Dim A	N×5.08±2.0
Dim B&C	(N-1)×5.08
N = Number of poles	
Poles	Tolerance
2-6p	±0.15
7-12p	±0.20
13-18p	±0.30
19-24p	±0.40

PART NO.: 0Q xx 5 4 x 0 00J0 G

No. of poles	Body Color	RoHS compliant
02 2 poles	0 Black (RAL9005)	(lead<4%)
03 3 poles	2 Red (RAL3001/D)	In copper Alloy
...	3 Orange(RAL2011/P)	
...	4 Yellow(RAL1018/A)	
24 24 poles	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title			
					linear	angles		TERMINAL BLOCK					
						X.±0.5		PLUGGABLE SOCKET,CLOSE TYPE,VERTICAL					
						X.X±0.3							
						X'±1°		scale		dwg no			
					dr	HANKE FENG	040314			sheet 1 of 1		size	
					engr	HANKE FENG	040314			0Qxx54x000J0G		A4	
					chr	SHI JUN	040314						
					appd	SHI JUN	040314						
sheet index		revision		A						type		CUSTOMER Drawing	
		sheet		1									