


## PC 4/10-G-7,62

Order No.: 1804878

The figure shows a 5-pos. version of the product

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1804878>

Header, Nominal current: 20 A, Nom. voltage: 400 V, Pitch: 7.62 mm,  
Number of positions: 10, Color: green, Assembly: Soldering

### Commercial data

|                          |                    |
|--------------------------|--------------------|
| EAN                      | 4017918046316      |
| Pack                     | 50 pcs.            |
| Customs tariff           | 85366990           |
| Weight/Piece             | 0.01793 KG         |
| Catalog page information | Page 370 (CC-2009) |

### Product notes

WEEE/RoHS-compliant since:  
01/01/2003



[http://  
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)  
Please note that the data given  
here has been taken from the  
online catalog. For comprehensive  
information and data, please refer  
to the user documentation. The  
General Terms and Conditions of  
Use apply to Internet downloads.

### Technical data

#### Dimensions / positions

|                     |            |
|---------------------|------------|
| Pitch               | 7.62 mm    |
| Dimension a         | 68.58 mm   |
| Number of positions | 10         |
| Pin dimensions      | 1 x 0,8 mm |
| Hole diameter       | 1.3 mm     |

#### Technical data

|                                    |        |
|------------------------------------|--------|
| Insulating material group          | I      |
| Rated surge voltage (III/3)        | 6 kV   |
| Rated surge voltage (III/2)        | 6 kV   |
| Rated surge voltage (II/2)         | 6 kV   |
| Rated voltage (III/2)              | 630 V  |
| Rated voltage (II/2)               | 630 V  |
| Connection in acc. with standard   | EN-VDE |
| Nominal current $I_N$              | 20 A   |
| Nominal voltage $U_N$              | 400 V  |
| Maximum load current               | 20 A   |
| Insulating material                | PA     |
| Inflammability class acc. to UL 94 | V0     |

#### Certificates / Approvals



Certification

BV, CSA, CUL, DNV, GL, GOST, LR, RS, UL

#### CSA

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 20 A  |

#### CUL

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 35 A  |

#### UL

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
| Nominal current $I_N$ | 35 A  |

#### Accessories


| Item                | Designation              | Description                                                                                                                                                                               |
|---------------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Assembly</b>     |                          |                                                                                                                                                                                           |
| 1827570             | BF-PC 4                  | Mounting flange, is snapped onto the left and right of the headers, for screw connection with PC 4/...-STF-7.62                                                                           |
| <b>Marking</b>      |                          |                                                                                                                                                                                           |
| 1051993             | B-STIFT                  | Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm                                                                               |
| 0804549             | SK 7,62/3,8:FORTL.ZAHLEN | Marker card, printed horizontally, self-adhesive, 10-section marker strip, 12 identical decades marked 1-10, 11-20 etc. up to 91-99, sufficient for 120 terminal blocks                   |
| 0805153             | SK 7,62/3,8:SO           | Marker card, special printing, self-adhesive, labeled acc. to customer requirements, 12 identical marker strips per card, max. 25-position labeling per strip, color: white               |
| 0803906             | SK U/3,8 WH:UNBEDRUCKT   | Unprinted marker cards, DIN A4 format, pitch as desired, self-adhesive, with 40 stamped marker strips, 185 mm strip length, can be labeled with the CMS system or manually with the M-PEN |
| <b>Plug/Adapter</b> |                          |                                                                                                                                                                                           |
| 1600027             | CP-HCC 4                 | Coding profile, Color: red                                                                                                                                                                |

#### Additional products


| Item           | Designation         | Description                                                                                                                                          |
|----------------|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>General</b> |                     |                                                                                                                                                      |
| 1880151        | PC 4 HV/10-STF-7,62 | Plug component, Nominal current: 20 A, Nom. voltage: 800 V, Pitch: 7.62 mm, Number of positions: 10, Connection type: Screw connection, Color: green |
| 1804988        | PC 4/10-ST-7,62     | Plug component, Nominal current: 20 A, Nom. voltage: 400 V, Pitch: 7.62 mm, Number of positions: 10, Connection type: Screw connection, Color: green |
| 1828320        | PC 4/10-STF-7,62    | Plug component, Nominal current: 20 A, Nom. voltage: 400 V, Pitch: 7.62 mm, Number of positions: 10, Connection type: Screw connection               |
| 1840117        | PCC 4/10-ST-7,62    | Plug component, Nominal current: 20 A, Nom. voltage: 400 V, Pitch: 7.62 mm, Number of positions: 10, Connection type: Crimp connection               |

## Diagrams/Drawings

### Drilling plan/solder pad geometry




### Diagram



The illustration shows the derating curve for plugs PC 5/...-ST-7,62 in combination with header PC 4/...-G-7,62.

### Dimensioned drawing



**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2010 Phoenix Contact  
Technical modifications reserved;