


Birnenlampen (Notbeleuchtung)

BL

Sockel E14

(26 x 57 mm)

Spannung	Ausf.	Leistung	Artikel-Nr.	EAN 4021553....
6V	klar	10W	00980610	252698
	klar	15W	00980615	252704
12V	klar	15W	00701215	252032
	klar	25W	00701225	252049
24V	klar	5W	00982405	252735
	klar	10W	00982410	252742
	klar	15W	00982415	252759
	klar	25W	00982425	252766
42V	klar	5W	00984205	252797
	klar	15W	00984215	252988
	klar	25W	00984225	252803
65V	klar	10W	00706510	252131
	klar	15W	00986515	252995
	klar	25W	00986525	252254
80V	klar	15W	00708015	252162
	klar	25W	00708025	252179
110-140V	klar	6-10W	00981410	252810
	klar	10-15W	00981415	252827
130V	klar	15W	00981315	252834
	klar	25W	00981325	252841
235V	klar	15W	00982215	252858
	TV-blau	15W	0098TV15	252919
	i-matt	15W	00982115	252117
	klar	25W	00982225	252926
	TV-blau	25W	0098TV25	252940
	klar	40W	00702240	252360
220-260V	klar	6-10W	00982610	252957
	klar	10-15W	00982615	252964
260V	klar, stossfest	15W	00706215	252209
	klar	25W	00982625	252971



AGL

