



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	O	REL PER 96-1164-005	10JUN96	LO	BB
	A	REVISED PER ECO-17-002887	31AUG2017	RS	DR



- 1 INSULATION $\varnothing$ 3.43 [$\varnothing$.135] MAX.
- 2 FITS TAB 0.81 [.032] THK.
- 3

MATERIAL:
BODY : BRASS PER ASTM B36, 0.46 ± 0.05 [.018 $\pm$.002].
SLEEVE : COPPER PER ASTM B152.
INSULATION : NYLON PER ASTM D4066.
- 4

FINISH:
BODY & SLEEVE : TIN PLATE 0.00254 [.000100] MIN. EXT. THK PER ASTM B545.



FITS "250" SERIES
FASTON TAB

—	LOOSE PIECE	184262-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: -	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 29MAY96	 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M ELLIS 29MAY96					
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: - -		0 PLC ± - 1 PLC ± - 2 PLC ± 0.38 [.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD B BARE 29MAY96	NAME RECEPTACLE, 250 SERIES, LOW INSERTION FORCE, FASTON™, PIDG™, WIRE SIZE, 22-18 AWG				
					PRODUCT SPEC -					
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: - -		MATERIAL	FINISH 	APPLICATION SPEC 114-1002	SIZE A3	CAGE CODE 00779	DRAWING NO C=184262	RESTRICTED TO -
						WEIGHT -				
CUSTOMER DRAWING							SCALE 6:1	SHEET 1 OF 1	REV A	