

TWO HOLE HYLUG™ CODE CONDUCTOR STANDARD BARREL (Continued)





Fig. 1




Fig. 2




Fig. 3

C-48

Catalog Number	Fig #	Conductor		Stud Hole Size	Stud Hole Spacing	Tongue Width	Figure Dimensions			Dieless (# of crimps)	▲ Installation Tooling					Wire Strip Length
		AWG	*** MM ²				(B)	(T)	(L)		Mechanical MD6, OUR840, MD7-34R	Hydraulic BCT500HS, Y500CTHS	Y35, Y39, Y750, Y46*, PAT750	Color Code	Die Index	
YA32L-2TC38E5	1	400 kcmil		3/8"	1-1/16"	1.40"	1.19"	.19"	3.75"	Y644M (1)	W32VT (2)	W32VT (2) W32RT (2)	U32RT (2) U30ART (2)	Blue	19	1-1/4"
YA32L-2TC38E5-45	2								3.66"							
YA32L-2TC38E5-90	3								2.52"							
YA32L-2TC38	3								3.69"							
YA32-2L	1								3.75"							
YA32-2L-45	2								3.66"							
YA32-2L-90	3	450 kcmil		3/8"	1"	1.40"	1.19"	.19"	2.52"		W33VT (2)	W33VT (2) W33RT (2)	U33RT (2)	Gray	326	1-9/16"
YA33-2LN	1								5.23"							
YA33-2LN-45	2								5.10"							
YA33-2LN-90	3								3.70"							
YA342LN	1			1/2"	1-3/4"	1.48"	1.50"	.21"	5.06"		W34VT (2)	W34VT (2) W34RT (2)	U34RT (2) U31ART (2)	Brown	20	1-7/16"
YA342LN-45	2								5.00"							
YA342LN-90	3								3.73"							
YA34L-2TC12	1	500 kcmil	240	1/2"	1-1/4"	1.52"	1.27"	.23"	4.38"							
YA34L-2TC12-45	2								4.31"							
YA34L-2TC12-90	3								3.04"							
YA34L-2TC14E2	1			1/4"	3/4"	1.52"	1.27"	.23"	3.44"							
YA34L-2TC14E2-45	2								3.37"							
YA34L-2TC14E2-90	3								2.10"							
YA34L-2TC38	1			3/8"	1"	1.52"	1.27"	.23"	3.88"							
YA34L-2TC38-45	2								3.81"							
YA34L-2TC38-90	3								2.54"							
YA34-2L	1			3/8"	1"	1.55"	1.27"	.23"	3.94"							
YA34-2L-45	2								3.87"							
YA34-2L-90	3								2.59"							
YA35-2L	1	550 kcmil	-	3/8"	1-1/8"	1.65"	1.69"	.25"	4.64"		-	-	U35RT (2)	Yellow	21	1-3/4"
YA35-2L-45	2								3.95"							
YA35-2L-90	3								2.60"							
YA35-2LN	1			1/2"	1-3/4"	1.65"	1.69"	.25"	5.07"							
YA35-2LN-45	2								3.73"							
YA35-2LN-90	3								4.36"							
YA362LN	1	600 kcmil	300	1/2"	1-3/4"	1.74"	1.38"	.27"	5.21"		-	-	U36RT (2) U32ART (2)	Green	22	1-3/4"
YA362LN45	2								3.81"							
YA362LN90	3								4.23"							
YA36L-2TC38	1			3/8"	1"	1.73"	1.38"	.27"	4.21"							
YA36L-2TC38-45	2								2.81"							
YA36L-2TC38-90	3								4.40"							
YA37-2L	1	650 kcmil	-	3/8"	1-1/8"	1.80"	1.39"	.27"	4.37"		-	-	U37RT (2)	Orange	23	1-15/16"
YA37-2L-45	2								2.96"							
YA37-2L-90	3								5.27"							
YA37-2LN	1			1/2"	1-3/4"	1.80"	1.39"	.27"	5.25"							
YA37-2LN-45	2								3.84"							
YA37-2LN-90	3								4.48"							
YA38-2L	1	700 kcmil	-	3/8"	1-1/8"	1.84"	1.45"	.27"	4.42"		-	-	U38RT (2)	Pink	400	1-15/16"
YA38-2L-45	2								3.23"							
YA38-2L-90	3								5.35"							
YA38-2LN	1			1/2"	1-3/4"	1.81"	1.45"	.27"	5.29"							
YA38-2LN-45	2								3.84"							
YA38-2LN-90	3								3.84"							

-- Color code not assigned.

▲ See tooling section of this catalog for complete tool and die listings.

◆ For applications greater than 2000 volts consult cable manufacturer for voltage stress relief instructions.

* Use PUADP-1 adapter with "U" dies in Y46 HYPRESS™.

** P-RT die sets for use in Y46 HYPRESS™ only, PUADP-1 adapter not required.

*** The MM² conductor sizes listed are the recommendations for Class 2 conductor.