

Part Search



Part Number . . .

FFA.00.250.CTAC27Z

Size/Series 00 / 00

[Demande d'offres](#)

MECHANICAL DETAILS

Shell Style/Model FFA*: Straight plug with cable collet and nut for fitting a bend relief



Keying Circular (can rotate)

Housing Material Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

Cable Fixing C27: 2.3 - 2.7 mm **NEW COLLET**

Variant Z : Nut for fitting a bend relief

	A	L	M
mm.	6.4	33.5	25.5
in.	0.25	1.32	1.00



MECHANICAL DETAILS

Insert Configuration 0.25 : 1 Coax (50 Ohm)

Insulator T: PTFE

Specifications

Contact Type: Coaxial 50 Ohm (Solder)

Max. Matings: 5000

Contact Dia.: 0.7 mm (0.028in)

Bucket Dia.: 0.6 mm (0.024in)

R (max): 6.1 mOhm

Vtest: 2100 V (AC), 3000 V (DC)

Rated Current: 4 A (AC/DC)

Impedance: 50 Ohm

VSWR: 1.09 + 0.11 * f/GHz

Cable type: RG 316 /U

MECHANICAL DETAILS

Endurance (Shell) 3839 mating cycles

F ret (min): 100 N

IP Rating 50

Catalog



[Copyright](#) [Privacy policy](#) [Product safety](#)