







ASSEMBLY




SECTION A-A




SECTION B-B




BOX - INSIDE



STEEL INNER PANEL



LID - INSIDE



Polycarbonate Version Only
UL US LISTED
 File #E65324
 NEMA 4, 4X

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
 Solid models of this enclosure available in STEP or IGES.
 Contact Factory mjm@hammondmfg.com

NOTE

Purchased assembly includes box, styled lid, 4 cover screws, and preformed silicone gasket.
 General Purpose ABS version is not UL approved. (Matl UL94 - HB)
 Polycarbonate version is UL 508 approved. (Matl UL94 - V0)

Recommended Cover screw torque -- 2.5 lbf-in (30 cN-m)

1555E

1555E Regular Enclosure

General Purpose ABS RAL-7035	1555EGY
------------------------------	---------

Polycarbonate RAL-7035	1555E2GY
------------------------	----------

ACCESSORIES

Steel Inner Panels	1554EPL
--------------------	---------

Steel Panel / P.C. Board Machine Screw [M3 x 8mm Plated]	1591MM100
--	-----------

Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated]	1598ATS100
--	------------

Cover Screws (Pkg 4)	SC1554
----------------------	--------

[M4 X 20mm Stainless Steel]	
-----------------------------	--

HAMMOND MANUFACTURING™
1555E
www.hammondmfg.com