





MATERIAL NO.	ENGINEERING P/N	CARRIER STYLE
196060004	C-5293Z	METAL STRIP
196060005	C-5293	LOOSE PIECE
196060006	C-5293T	TAPE MOUNT



METAL CARRIER STRIP,
METAL STRIP PARTS ONLY



PARTS ON TAPE
SCALE: NONE



SECTION A-A

NOTES:

1. MATERIALS:

HOUSING: 94V-2 NYLON, YELLOW

TERMINAL: BRASS, .018/0.46 THICK REF., MATTE TIN PLATED

① FERRULE: COPPER ALLOY, MATTE TIN PLATED

2. ACCEPTS TAB SIZE .250 x .032 (6.35 x 0.81).

3. MWD = MAXIMUM WIRE INSULATION DIAMETER.

4. PARTS ARE ROHS COMPLIANT.

RLS, FERRULE MAT'L EC NO: WNA2010-0610 DRAWN: ETHRODAHL 2010/03/31 CHKD: JMACNEIL 2010/03/31 APPR: JMACNEIL 2010/04/12	REV A	DESCRIPTION A	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 5:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
				4 PLACES ± --- ± ---		DRAWN BY DATE ETHRODAHL 2010/03/31		TITLE FIQD FEMALE AVIKRIMP LOW PROFILE .250X.032 TAB, 12-10 AWG		
				3 PLACES ± --- ± ---		CHECKED BY DATE JMACNEIL 2010/03/31		MOLEX INCORPORATED		
				2 PLACES ± --- ± ---		APPROVED BY DATE JMACNEIL 2010/04/09		DOCUMENT NO. SD-19606-003		
				1 PLACE ± --- ± ---		MATERIAL NO. SEE CHART		SHEET NO. 1 OF 1		
				ANGULAR ±1/2°		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						