



www.ameripack.com

## Heavy-duty Shipping Cases



**Ameripack's Heavy-duty Shipping containers are designed and constructed to offer the ultimate in security and protection for your valuable products.**


**DESIGN:** Our Shipping Cases are formed by our **special ATA tooling** which creates molded-in **corner bumpers** and **stacking lugs**. The protruding bumpers offer additional protection, especially at every containers' weakest point - the corner. These bumpers absorb the impacts so your products don't. The molded-in lugs ensure stability when stacking cases.

**HARDWARE:** Our Shipping Cases utilize our standard **Heavy-duty hardware**

- 2" Aluminum valance extrusion (with silicone sealant and moisture gasket)
- Steel hinges, steel twist-draw latches, steel spring-loaded handles, and 9" lid stays

### STANDARD HARDWARE

Shell: High-density Polyethylene



2" Aluminum Valance w/ Channel



Steel Spring-loaded Handle



Steel Twist Draw Latch




4"x 1 7/8" Steel Hinge

Neoprene O-Ring Valance Gasket

9" Heavy-duty Lid Stay

### OPTIONAL HARDWARE



2" Aluminum Valance w/ 1/2" Flange

- Stainless Steel Padlock Hasp
- Stainless Steel Latch Protector
- Built-in Key Lock
- Pressure Relief Valve
- Humidity Indicator
- Label and Card Holders
- Telescoping Handle
- Removeable Casters
- Built-in Edge Wheels

**USE:** Heavy Duty Shipping Cases are best for products which may be shipped frequently as freight or luggage, or for items which may be heavy (over 40 pounds), delicate, and/or valuable. Items such as computers, commercial tooling, video equipment, and motorcycle engines.

**WHY Ameripack?:** Our vacuum-formed Shipping Cases offer industry leading value. Compared to other styles of shipping case, our durable and lightweight cases offer longer case life with lower shipping costs and lower cost of ownership.

### FEATURES:

- High-density polyethylene plastic for strength and impact resistance
- Molded-in bumpers for unsurpassed product protection
- Molded-in ribs and channels for stacking stability
- 2 1/8" valance and heavy-duty hardware for high quality security
- Able to meet stringent ATA 300 - Cat. 1 and MIL specifications
- Withstand temperatures from -80 degrees F to +180 degrees
- Solvent, moisture, and water-resistant
- Hundreds of standard sizes available
- Almost limitless custom options

### BENEFITS:

- Designed and constructed for long term durability and reuse
- Damage and corrosion resistance plus lightweight means reduced shipping costs
- Bel-Air craftsmanship ensures that the case takes the beating, not your delicate equipment

### APPLICATIONS:

- Broadcast and video equipment
- Industrial and commercial tools
- Computers and electronics
- Surveying and seismographic devices
- Industrial and commercial lighting
- Diagnostic and testing equipment
- Rare and valuable collectables

**Call 800-456-7963 now for instant case recommendations, design and pricing!**


## Heavy Duty Thermoform Shipping Cases From:



### Standard Hardware

**Shell:** High Density Polyethylene  
Stock Color = Silver

**Valance:** 2" Aluminum Valance



**Lid Stay:** 9" Heavy Duty Lid Stay

**Hinge:** 4" X 1.88" Steel hinge



**Latch:** Steel Twist Draw Latch




**Handle:** Steel Spring-Loaded Handle



**O-Ring:** Neoprene Gasket

### Optional Hardware

Stainless Steel Padlock Hasp  
Stainless Steel Latch Protector  
Built-In Key Lock  
Pressure Relief Valve  
Telescoping Handle / Casters  
Humidity Indicator  
Label and Card Holders



| Part #   | Length | Width | Heights Variable in 0.25" Increments |              |              | Weight | Standard # |         |              |
|----------|--------|-------|--------------------------------------|--------------|--------------|--------|------------|---------|--------------|
|          |        |       | Total Height                         | Lid Height   | Base Height  |        | Handles    | Latches | Hinges/Stays |
| AP1212S  | 12     | 12    | 9 to 14                              | 4.5 to 7     | 4.5 to 7     | 9      | 1          | 2       | 2/1          |
| AP1212M  | 12     | 12    | 12.5 to 18                           | 4.5 to 7     | 8 to 11      | 10     | 2          | 2       | 2/1          |
| AP1212D  | 12     | 12    | 16 to 22                             | 8 to 11      | 8 to 11      | 11     | 2          | 2       | 2/1          |
| AP1512S  | 15     | 12    | 10 to 16                             | 5 to 8       | 5 to 8       | 11     | 1          | 2       | 2/1          |
| AP1616S  | 16     | 16    | 8 to 15                              | 4 to 7.5     | 4 to 7.5     | 12     | 1          | 2       | 2/1          |
| AP1616M  | 16     | 16    | 13.5 to 20                           | 4 to 7.5     | 9.5 to 12.5  | 13     | 2          | 2       | 2/1          |
| AP1616D  | 16     | 16    | 19 to 25                             | 9.5 to 12.5  | 9.5 to 12.5  | 14     | 2          | 2       | 2/1          |
| AP1814S* | 18     | 14.5  | 8 to 14                              | 4 to 7       | 4 to 7       | 12     | 1          | 2       | 2/1          |
| AP1814M* | 18     | 14.5  | 12 to 18                             | 4 to 7       | 8 to 11      | 13     | 2          | 2       | 2/1          |
| AP1814D* | 18     | 14.5  | 16 to 28                             | 8 to 14      | 8 to 14      | 16     | 2          | 2       | 2/1          |
| AP1910S  | 19     | 10    | 10 to 11                             | 5 to 5.5     | 5 to 5.5     | 11     | 1          | 2       | 2/1          |
| AP1910M  | 19     | 10    | 15.5 to 16                           | 5 to 5.5     | 11 to 11.5   | 12     | 2          | 2       | 2/1          |
| AP1910D  | 19     | 10    | 22 to 23                             | 11 to 11.5   | 11 to 11.5   | 13     | 2          | 2       | 2/1          |
| AP2112S  | 21     | 12    | 9 to 12                              | 4.5 to 6     | 4.5 to 6     | 13     | 1          | 2       | 2/2          |
| AP2112M  | 21     | 12    | 14.5 to 17.5                         | 4.5 to 6     | 10 to 11.5   | 14     | 2          | 2       | 2/2          |
| AP2112D  | 21     | 12    | 20 to 23                             | 10 to 11.5   | 10 to 11.5   | 15     | 2          | 2       | 2/2          |
| AP2218S* | 22     | 18    | 6 to 13                              | 3 to 6.5     | 3 to 6.5     | 15     | 1          | 2       | 2/2          |
| AP2218M* | 22     | 18    | 13.5 to 16.5                         | 5 to 6.5     | 8.5 to 10    | 17     | 2          | 2       | 2/2          |
| AP2218D* | 22     | 18    | 17 to 20                             | 8.5 to 10    | 8.5 to 10    | 19     | 2          | 2       | 2/2          |
| AP2424S* | 24     | 24    | 11 to 14                             | 5.7 to 7     | 5.5 to 7     | 20     | 1          | 4       | 2/2          |
| AP2424M* | 24     | 24    | 16 to 19.5                           | 5.5 to 7     | 10.5 to 12.5 | 22     | 4          | 4       | 2/2          |
| AP2424D* | 24     | 24    | 21 to 25                             | 10.5 to 12.5 | 10.5 to 12.5 | 24     | 4          | 4       | 2/2          |

\* Indicates Stock Shell

107 N Gold Dr · Robbinsville, NJ 08691 · Phone: (609)259-7004 · Fax: (609)259-8975 · e-mail: sales@ameripack.com

Sheet 1 of 2

## Heavy Duty Thermoform Shipping Cases From:



| Part #   | Length | Width | Heights Variable in 0.25" Increments |                   |              | Weight | Standard # |         |              |
|----------|--------|-------|--------------------------------------|-------------------|--------------|--------|------------|---------|--------------|
|          |        |       | Total Height                         | Lid Height        | Base Height  |        | Handles    | Latches | Hinges/Stays |
| AP2521S  | 25.5   | 21    | 12 to 15                             | 6 to 7.5          | 6 to 7.5     | 18     | 1          | 2       | 2/2          |
| AP2521M  | 25.5   | 21    | 16 to 19.5                           | 6 to 7.5          | 10 to 12     | 20     | 2          | 2       | 2/2          |
| AP2521D  | 25.5   | 21    | 20 to 24                             | 10 to 12          | 10 to 12     | 22     | 2          | 2       | 2/2          |
| AP2712S  | 27     | 12.5  | 7 to 8.5                             | 3.5 to 4.5        | 3.5 to 4.5   | 14     | 1          | 2       | 2/2          |
| AP2712M  | 27     | 12.5  | 10.5 to 12                           | 3.5 to 4.5        | 7 to 7.5     | 17     | 2          | 2       | 2/2          |
| AP2712D  | 27     | 12.5  | 14 to 15                             | 7 to 7.5          | 7 to 7.5     | 20     | 2          | 2       | 2/2          |
| AP2727D  | 27     | 27    | 14 to 21                             | 7 to 10.5         | 7 to 10.5    | 28     | 4          | 4       | 2/2          |
| AP2818S* | 28     | 18    | 11 to 15                             | 5.5 to 7.5        | 5.5 to 7.5   | 20     | 1          | 2       | 2/2          |
| AP2818M* | 28     | 18    | 14 to 17.5                           | 5.5 to 7.5        | 8.5 to 10    | 22     | 2          | 2       | 2/2          |
| AP2818D* | 28     | 18    | 17 to 20                             | 8.5 to 10         | 8.5 to 10    | 24     | 2          | 2       | 2/2          |
| AP2825S  | 27.5   | 25    | 13 to 15                             | 6.5 to 7.5        | 6.5 to 7.5   | 26     | 4          | 4       | 2/2          |
| AP2825M  | 27.5   | 25    | 17 to 23                             | 6.5 to 7.5        | 10.5 to 15.5 | 29     | 4          | 4       | 2/2          |
| AP2825D  | 27.5   | 25    | 21 to 31                             | 10.5 to 15.5      | 10.5 to 15.5 | 32     | 4          | 4       | 2/2          |
| AP3012S  | 30     | 12    | 9 to 12                              | 4.5 to 6          | 4.5 to 6     | 16     | 1          | 2       | 2/2          |
| AP3012M  | 30     | 12    | 14.5 to 18                           | 4.5 to 6          | 10 to 12     | 18     | 2          | 2       | 2/2          |
| AP3012D  | 30     | 12    | 20 to 24                             | 10 to 12          | 10 to 12     | 20     | 2          | 2       | 2/2          |
| AP3018D  | 30     | 18    | 17 to 22                             | 8.5 to 11         | 8.5 to 11    | 24     | 2          | 2       | 2/2          |
| AP3120S  | 31     | 20    | 9 to 16                              | 4.5 to 8          | 4.5 to 8     | 26     | 2          | 2       | 2/2          |
| AP3122S* | 31     | 22    | 10 to 14                             | 5 to 7            | 5 to 7       | 27     | 2          | 2       | 2/2          |
| AP3122M* | 31     | 22    | 15 to 19                             | 5 to 7            | 10 to 12     | 29     | 2          | 2       | 2/2          |
| AP3122D* | 31     | 22    | 20 to 24                             | 10 to 12          | 10 to 12     | 32     | 2          | 2       | 2/2          |
| AP3214S  | 32     | 14    | 12 to 16                             | 6 to 8            | 6 to 8       | 24     | 2          | 2       | 2/2          |
| AP3214M  | 32     | 14    | 14 to 18                             | 6 to 8            | 8 to 10      | 26     | 2          | 3       | 3/2          |
| AP3214D  | 32     | 14    | 16 to 20                             | 8 to 10           | 8 to 10      | 28     | 2          | 3       | 3/2          |
| AP3418S  | 34     | 17    | 14 to 17                             | 7 to 8.5          | 7 to 8.5     | 30     | 2          | 3       | 3/2          |
| AP3424S* | 34     | 24    | 15 to 21                             | 7.5 to 10.5       | 7.5 to 10.5  | 35     | 4          | 4       | 3/2          |
| AP3424M* | 34     | 24    | 19 to 24.5                           | 7.5 to 10.5       | 11.5 to 14   | 38     | 4          | 4       | 3/2          |
| AP3424D* | 34     | 24    | 23 to 28                             | 11.5 to 14        | 11.5 to 14   | 41     | 4          | 4       | 3/2          |
| AP3620D  | 36     | 20    | 20 to 24                             | 10 to 12          | 10 to 12     | 36     | 4          | 3       | 3/2          |
| AP4325S* | 43     | 25    | 8 to 9                               | 4 to 4.5          | 4 to 4.5     | 42     | 4          | 4       | 4/2          |
| AP4325M* | 43     | 25    | 16.5 to 22.5                         | 4 to 4.5/7 to 8.5 | 12.5 to 13.5 | 45     | 4          | 4       | 4/2          |
| AP4325D* | 43     | 25    | 25 to 27                             | 12.5 to 13.5      | 12.5 to 13.5 | 48     | 4          | 4       | 4/2          |

\* Indicates Stock Shell

107 N Gold Dr · Robbinsville, NJ 08691 · Phone: (609)259-7004 · Fax: (609)259-8975 · e-mail: sales@ameripack.com

Sheet 2 of 2