


8928 Series

BNC Straight



Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0.

Insulator: PE-606.

Center Contact: Copper Alloy, Gold Plated.

Mounting Post: Metal, Tin Plated.





Solder Tail: Copper, Wire, Tin Plated.

Washer: Metal, Nickel Plated.


Nut: Copper Alloy, Nickel Plated.

Features:


- * Available in 50 & 75 ohm version.
- * Bayonet locking.
- * Choice of two profile (A & B).




P.C. Board Layout for Type A




Recommended Mounting Hole.
Maximum Panel Thickness: 5.5mm.
Recommended Mounting Torque: 12 Inch-Pounds Max.



P.C. Board Layout for Type B



Lock Washer



1/2-28UNef-2B
Clamp Nut

Length	A	B
X	15.8	13.16
Y	10.16	8.55

Ordering information

8928-

Series

A

A: Type A

B: Type B

(Profile)

1

1: With Washer & Nut

Blank: Without Washer & Nut

S

S: Straight

-50

50: 50 ohm

75: 75 ohm

A

A: Tray Package