


**General ordering data**

Order No.	1770370000
Part designation	ZDU 4-2/2AN
Version	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
EAN	4032248143177
Qty.	100 pc(s).

Product notes

Note, ordering data	The rated voltage is reduced to 400 V when using the cross-connection.
Product description	The compact terminal range for conductor cross-sections 0.13 to 16 mm ²
Note, accessories	The rated voltage is reduced to 250 V when using the shield bus LS 2.8 (1056400000).

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA97ATEX4677U
Download, German	KEMA97ATEX4677U_d.pdf
Download English	KEMA97ATEX4677U_e.pdf
ATEX voltage	550 V
ATEX current	28 A
ATEX conductor cross-section	4 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	dark beige
Connection direction	Inclined / angled
End plate required	Yes
Explosion-tested version "Ex e"	Yes

Additional technical data

Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	Z-series
Type of connection	Clamped
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	35 A
Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 10

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	4 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²
Type of connection	Tension clamp connection
2nd type of connection	clamped
Connection direction	Inclined / angled
No. of connections	2
Stripping length	10 mm
Blade size	0.6 x 3.5 mm
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	6 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	4 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	4 mm ²
Twin wire-end ferrule, min.	0.5 mm ²
Twin wire end ferrule, max.	1.5 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 10
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	5.26 mm ²

Conductors for clamping (rated connection)**Dimensions**

Width	6.1 mm
Height of lowest version	46 mm
Length	61.5 mm
TS 35 offset	33 mm

Rating data

Rated cross-section	4 mm²
Rated voltage	800 V
Rated impulse voltage	8 kV
Rated current	32 A
Standards	IEC 60947-7-1
Current with max. conductor	32 A
Pollution severity	3

UL rating data

Voltage (UL)	600 V
Current (UL)	33 A
Min. cross-section (UL)	AWG 26
Max. cross-section (UL)	AWG 10

Approvals

Approvals institutes

**Downloads**

STEP	1770370000_30072_ZDU_4_2_2AN_STP.stp
------	--------------------------------------

Classifications

eClass 4.1	27-14-11-20
eClass 5.0	27-14-11-20
eClass 5.1	27-14-11-20

Similar products

Order No.	Part designation	Version
8670750000	ZDK 4-2	Modular terminal, 4 mm², Tension clamp connection, Wemid, dark beige, TS 35
8670850000	ZDK 4-2 BL	Modular terminal, 4 mm², Tension clamp connection, Wemid, blue, TS 35

8709760000	ZDK 4-2 EL	Modular terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
8671050000	ZDK 4-2 PE	Modular terminal, 4 mm ² , Tension clamp connection, Wemid, green, TS 35
8671080000	ZDK 4-2 V	Modular terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
8671120000	ZDK 4-2/DU-PE	Modular terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1905170000	ZDK 4-2/N/L	Modular terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1770840000	ZDU 4-2/2AN BL	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, blue, TS 35
1770360000	ZDU 4-2/3AN	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1770860000	ZDU 4-2/3AN BL	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, blue, TS 35
1770870000	ZDU 4-2/3AN OR	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, Orange, TS 35
1806980000	ZDU 4-2/4AN	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1806990000	ZDU 4-2/4AN BL	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, blue, TS 35