


1 | 2 | 3 | 4

FCI P/N (NOTE 1)	LENGTH "L" (NOTE 1)
57660-XXXX	XXX



SPECIFICATIONS	
ST2	SC
INSERTION LOSS	0.5dB MAX
RETURN LOSS	55dB MIN
FIBER PROTRUSION	50nm MAX
APEX OFFSET	45um MAX
FIBER UNDERCUT	SEE TELECORDIA GR-326

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		Electronics	
ltr	ecm no	dr	date	NOMINALS ONLY	projection	FCI	
A	V11336	JJK	5/25/01	UNLESS NOTED		www.fciconnect.com	
				linear		title	
				angles		CA, FC2-ST2, 3mm, SM-8.3	
				dr	J. KILE	product family	
				enfr	G. WARNER	FIBER OPTICS	
				chr	G. WARNER	size dwg no	
				appd	G. WARNER	213	
sheet	revision	A				scale	
index	sheet	1				A4	
						1:1	
						57660	
						sheet	
						1 of 1	
						code	
						22526	

NOTES:  
 1. FCI P/N CONSISTS OF THE DWG NO, A DASH A SUFFIX Y AND A SUFFIX XXX WHERE  
 Y IS THE UNIT OF LENGTH(Y=M IS METERS AND Y=F IS FEET) AND WHERE XXX IS THE  
 LENGTH "L"  
 (EX: 57660-F004 IS 4 FT IN LENGTH)

Tous droits strictement reserves. Reproduction ou communication a des tiers.  
 Interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.  
 Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any  
 form whatever is not permitted without written authority from the proprietor.  
 Property of FCI. Copyright FCI.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI:](#)

[57660-M001](#)