

## Product Search

Item no...

## Product Catalog

### Products

[Lamps & LED-Lamps](#)

[LED lamps](#)

[StarLEDs](#)

[T6,8](#)

## Markets

[Automotive](#)

[Aviation](#)

[Gaming](#)

[Illumination](#)

[Transport](#)

[Custom Projects](#)

## Product details

**Article: 1507125W3D**



**StarLED, T6.8 LED-Lamp, 12V  
AC/DC, cold white**

### Description

Designation: StarLED, T6.8 LED-Lamp, 12V  
AC/DC, cold white

Product range: StarLED

### Optical features

Colour: cold white

Coordinates in colour 0,31 / 0,32

Number of LEDs: 1

Typ. Luminous intensity: 425 mcd (at DC current)

LED epoxy type: diffused

### Electrical features

Operating Voltage: 12 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

DC current: 17 mA

### Mechanical features

Socket: T6.8

Length: 43 mm

Lamp size: T6.8

Diameter: 6,8 mm

### Thermal features

Operating temperature: -20...+60 °C

Storage temperature: -25...+80 °C

### Gallery

## Latest News

**2013-01-08**  
LEDs MADE EASY.  
>> [More details](#)

**2012-03-09**  
Successful  
surveillance audit  
according to ISO  
9001:2008  
>> [More details](#)

**2012-02-24**  
Latest Nichia LEDs in  
CML products  
>> [More details](#)



[Standard Image](#)

[Drawing](#)



Click on a small picture to select it. Click the large image to view full size.



**Multivoltage LED Lamps**  
Covering the voltage range of 6 to 32V  
Available in all colours and BA9s socket

