

97  
33

## KNIPEX MultiCrimp®

Crimping Pliers with quick changer magazine



97 33 01



97 33 02



**97 33 01**

Crimping pliers with round magazine and three interchangeable die sets for non-insulated open plug connectors (4.8 + 6.3 mm width) from 0.5 - 6.0 mm<sup>2</sup>; insulated terminals + plug connectors from 0.5 - 6.0 mm<sup>2</sup>; end sleeves (ferrules) from 0.25 - 6.0 mm<sup>2</sup>

**97 33 02**

Crimping pliers with round magazine and five interchangeable die sets for non-insulated open plug connectors (4.8 + 6.3 mm width) from 0.5 - 6.0 mm<sup>2</sup>; insulated terminals + plug connectors from 0.5 - 6.0 mm<sup>2</sup>; end sleeves (ferrules) from 0.25 - 6.0 mm<sup>2</sup>; non-insulated terminals and plug connectors from 0.5 - 10 mm<sup>2</sup>; non-insulated butt connectors from 1.5 - 10 mm<sup>2</sup>

**The MultiCrimp® Pliers are not available in the U.S.A.**



Compact, inexpensive and light-weight crimping pliers for fitting and repairs. The electrician needs only one tool now instead of five as before.

- just one tool for the most common crimping applications
- crimping dies changed quickly and easily without any additional tool
- secure and protected storage of the interchangeable dies in a round magazine
- comfortable, powerful crimping pliers in professional quality
- same reliable crimping results as with fixed crimping dies
- repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Chrome vanadium electric steel in special quality, oil-hardened
- Round magazine: plastic, fibreglass-reinforced



Changing position: service lever opens out for parallel jaw positioning



Changing the crimping dies: unlock the magazine position, take out the set of dies which the pliers have been pushed on



Fold in the service lever and press the pliers – ready for use again



Magazine for crimping dies can be carried on a belt



Clearly visible marking on the crimping dies with pictograms

The MultiCrimp® Pliers are not available in the U.S.A.

| Article No. | EAN<br>4003773- | ↔<br>mm                                                                |    | Pliers    | Handles                         |  |  | Applications                                   | Capacity<br>mm²          | AWG               | Number of<br>crimping<br>positions | ⚖<br>g |
|-------------|-----------------|------------------------------------------------------------------------|----|-----------|---------------------------------|--|--|------------------------------------------------|--------------------------|-------------------|------------------------------------|--------|
| 97 33 01    | 066927          | 250                                                                    | MM | burnished | with multi-com-<br>ponent grips |  |  | non-insulated, open plug-<br>type connectors   | 0.5 - 6.0                | 20 - 10           | 3                                  | 770    |
|             |                 |                                                                        |    |           |                                 |  |  | insulated terminals and<br>plug connectors     | 0.5 - 6.0                | 20 - 10           | 3                                  |        |
|             |                 |                                                                        |    |           |                                 |  |  | End Sleeves (ferrules)                         | 0.25 - 6.0               | 23 - 10           | 5                                  |        |
| 97 33 02    | 066934          | 250                                                                    | MM | burnished | with multi-com-<br>ponent grips |  |  | non-insulated, open plug-<br>type connectors   | 0.5 - 6.0                | 20 - 10           | 3                                  | 870    |
|             |                 |                                                                        |    |           |                                 |  |  | insulated terminals and<br>plug connectors     | 0.5 - 6.0                | 20 - 10           | 3                                  |        |
|             |                 |                                                                        |    |           |                                 |  |  | End Sleeves (ferrules)                         | 0.25 - 6.0               | 23 - 10           | 5                                  |        |
|             |                 |                                                                        |    |           |                                 |  |  | non-insulated terminals<br>and plug connectors | 0.5 - 10.0               | 20 - 7            | 4                                  |        |
|             |                 |                                                                        |    |           |                                 |  |  | non-insulated butt<br>connectors               | 1.5 - 4.0<br>6.0 + 10.0* | 15 - 11<br>10 + 7 | 3<br>2                             |        |
| 97 39 05    | 070078          | Crimping dies for non-insulated open plug-type connectors 4.8 + 6.3 mm |    |           |                                 |  |  |                                                |                          |                   |                                    |        |
| 97 39 06    | 070085          | Crimping dies for insulated terminals + plug connectors                |    |           |                                 |  |  |                                                |                          |                   |                                    |        |
| 97 39 08    | 070092          | Crimping dies for end sleeves (ferrules)                               |    |           |                                 |  |  |                                                |                          |                   |                                    |        |
| 97 39 13    | 070108          | Crimping dies for non-insulated terminals + plug connectors            |    |           |                                 |  |  |                                                |                          |                   |                                    |        |
| 97 39 30    | 070115          | Crimping dies for non-insulated butt connectors                        |    |           |                                 |  |  |                                                |                          |                   |                                    |        |
| 97 39 90    | 070061          | Quick Changer Magazine empty                                           |    |           |                                 |  |  |                                                |                          |                   |                                    |        |

\* compression joints in conformance to DIN 46267