




FEATURES:

- Converts equipment with two conductor .097" diameter. micro jacks for use with BNC cables
- The all metal construction allows operation in higher temperature environments

MATERIAL:

Body: Brass, corrosion resistant plating

Center Contact: Beryllium Copper, gold plating

RATINGS:

Operating Temperature.: +257° F. (+125° C.) Max.

Operating Voltage: 500 VRMS Max.

ORDERING INFORMATION: Model 4267

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90410 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com