





AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 5
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm²[5,180-13,100] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
G	14		D2	REVISED PER ECO-12-015539	28AUG12	KH

AMP WIRE RANGE	E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 TIN PLATE 0.00254[.000100] MIN EXT THICK
PER ASTM B545
- 3 TIN-LEAD(93-7) PLATE 0.00254[.000100]
MIN EXT THICK PER ASTM B545
(3% MIN LEAD CONTENT)
- 4 PART NUMBER NOT UL OR CSA APPROVED.
- 5 MAX RECOMMENDED OPERATING TEMPERATURE
IS 170°C MAX.

3	4	500	LOOSE PIECE	321632-1
5	2	500	LOOSE PIECE	321632
		QUANTITY	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-8-93	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 4-8-93					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD DE MILLER 4-8-93	NAME TERMINAL, HOOK TONGUE, SOLISTRAND™				
		PRODUCT SPEC —					
		MATERIAL COPPER PER ASTM B-152 ANNEALED	APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C-321632	RESTRICTED TO —
		 	WEIGHT —	CUSTOMER DRAWING		SCALE 8:1	SHEET 1 of 1