


Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 50mA / 12VDC
- Contact Resistance: 100m Ω Max.
- Insulation Resistance: 100M Ω Min.
- Dielectric Strength: 250VAC for 1 Minute

Mechanical Specifications:

- Operating Life: 50,000 Cycles
- Operating Temperature: -25°C to +70°C

Note:

- RoHS Compliant and Process Compatible with 260° solder

Tactile Switches
 101-TS6211T2602AC-EV, 101-TS6211T3202AC-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-TS6211T3202AC-EV](#) [101-TS6211T2602AC-EV](#)