

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190950139](#)
Status: **Active**
Description: Terminal Lugs for 14-16 AWG, Insulated Blue Sleeve, Stud Size 4 (M2.6), Length 20.22mm (.796")

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Ring and Spade Terminals
Series [19095](#)
Comments Type II Insulated; Class 1 and 2
Crimp Quality Equipment Yes
Mil-Spec AS17143-20, MS17143-20
Product Name Avikrimp™
Type Ring

Physical
Barrel Type Closed
Insulation Nylon (PA)
Material - Plating Mating Tin
Packaging Type Bag
Plating min - Mating 2.540µm (100µ")
Plating min - Termination 2.540µm (100µ")
Stud Size 4 (M2.6)
Wire Size AWG 14, 16

Material Info
Old Part Number BB-886-2

Reference - Drawing Numbers
Product Specification PS-19902-011, PS-19902-013
Sales Drawing SD-19095-006

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19095Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19095-0139](#)