

Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-LC Fiber Opt ..
- Part Drawings
- DXF-LC Duplex Co ..
- DWG-LC Duplex Co ..
- PDF-LC Duplex Co ..
- Specification Sheets
- PDF-LC Fiber Opt ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-LC Fiber Opt ..
- Stripping Templates
- PDF-LC Fiber Opt ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'FLCDS3.0BU'

Your search criteria matched only one product, shown below

FLCDS3.0BU



- TIA/EIA-604 FOCIS-10 compatible connectors
- Exceed TIA/EIA-568-B.3 requirements
- Insertion loss: 0.10dB average (multimode and singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- Non-optical disconnect maintains data transmission under tensile loads for jacketed cable
- Each simplex connector includes the following: one connector body/ferrule assembly, one crimp sleeve, one dust cap, and depending on the part number ordered, one boot for 900µ m buffered fiber and one boot for 1.6mm– 2.0mm jacketed cable or one boot for 3.0mm jacketed cable
- Each duplex connector includes two connector body/ferrule assemblies, two crimp sleeves, two dust caps, one duplex clip, and depending on the part number ordered, two boots for 1.6mm - 2.0mm jacketed cable, two boot for 3.0mm jacketed cable, or two boots for 900µ m buffered fiber
- LC duplex clip available separately for duplexing two simplex Panduit LC Connectors
- Fiber cable type: tight-buffered recommended
- Fiber cable size: accept 1.6mm – 2.0mm or 3.0mm jacketed cable, 900µm buffered fiber (noted in part description)
- For 250µm coated fiber termination, use 250 micron fiber build-up tube kit or fan-out kits
- Ferrule type: 1.25mm zirconia ceramic (highest durability for repeated matings)
- Field polish termination – Panduit recommends anaerobic adhesive
- Use field polish termination kit (FIELDKIT)

• Part Number	FLCDS3.0BU
• RoHS Compliancy Status	RoHS directive is not applicable
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	LC singlemode duplex fiber optic connector for 3.0mm jacketed cable installation.
• Product Type	LC Duplex Connectors
• Color	Blue
• Fiber Compatibility	9/125µm
• Fiber Cable Size	3.0mm
• Fiber Cable Type	Tight-buffered recommended
• Fiber Type	Singlemode
• Termination Style	Field Polish
• CE Compliant	No
• Ferrule Type	Zirconia Ceramic
• Pricing Description	LC Singlemode Dupl Connector With 3.0mm Boots - Field Polish
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.