


MICRO SWITCH

A DIVISION OF AMTHERPOLIS-HONEYWELL REGULATOR COMPANY
PHILADELPHIA, PENNSYLVANIA

FED. MFR. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
BAFI-3RNXI



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS (BOTH PLUNGERS)

OPERATING FORCE — — — 13/4 LBS. MAX.

OVERTRAVEL — — — .219 MIN.

SWITCH-BASIC REPLACEMENT — — BA-3RX717

ELECTRICAL DATA

CONTACT ARRANGEMENT
SINGLE POLE DOUBLE THROW
MAINTAINED CONTACT

BREAK DISTANCE
.036 MIN.

L224

20A 125, 250 OR 480VAC
1HP 125VAC, 2HP 250VAC
1/2A 125VDC, 1/4A 250VDC



RU

SCALE—FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) $\pm .030$
TWO PLACE (.00) $\pm .015$
THREE PLACE (.000) $\pm .005$
ANGLES $\pm$

WEIGHT

BAFI-3RNXI

M

DRAWING
NUMBER

ISSUE
9

REPLACES

RELEASE NO. SR 6953

2 Oct 57

1 Oct 57

CHECK

1 Oct 57

CHECK

ACG

25 AUG 83

CHECK

3 Oct 57

RLZ

CHECK

27 SEPT 57

K. A. F.

27 SEPT 57

FO-80378

DRAWN