


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
615	A	RELEASED	JWM	12/4/01	HYO	12/4/01	DJC	12/4/01
1355	B	Added 76-116 and 76-118	JWM	1/2/04	JC	1/2/04	JC	1/2/04


NOTES:

1. Rating: 1,200V, 12 Amps AC/DC
2. Materials:
 - Body-Polyamide (Nylon)
 - Plug - Bronze & Brass Nickel Plated
3. Lead Wire:
 - Jacket - Flexible PVC
 - Conductor: 0.75mm²
4. Temperature: -20°C ~ +80°C

Tenma Part No.	Length	Internal Resistance (mΩ)	Color
76-098	10 [25cm]	12	Black
76-099	10 [25cm]	12	Red
76-100	20 [50cm]	15	Black
76-101	20 [50cm]	15	Red
76-116	40 [100cm]	20	Black
76-118	40 [100cm]	20	Red

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
 HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
 BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
 CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
 USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
 FOR THE INTENDED USE AND ASSUME ALL RISK AND
 LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
 UNLESS OTHERWISE
 SPECIFIED,
 DIMENSIONS ARE
 FOR REFERENCE
 PURPOSES ONLY.

DRAWN BY: Jeff McVicker 12/4/01
 CHECKED BY: Hisham Odish 12/4/01
 APPROVED BY: Daniel Carey 12/4/01

DRAWING TITLE:
 Plug Leads, 4mm Straight Plug to Straight Jack
 SIZE DWG. NO. ELECTRONIC FILE REV
 A TA-458 TA-458.dwg B
 SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1