

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100042](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway 500W Twin Halogen Floodlight Stanchion Mount with GFCI Outlet Box and Switch, Cord Type 12/3 SOOW, Cord Length 0.457m (1.50')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130110
NEMA Configuration	NEMA 5-20
NEMA Rating	Rain Tight
Outlet	Side
Overview	Wide-Area Lighting Products
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678899220
Physical	
Cord Length - Primary	0.457m (1.50')
Cord Length - Secondary	N/A
Depth	1.16m (3.80')
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	2.29m (7.50')
Length	1.16m (3.80')
Material - Globe	Tempered Glass
Material - Guard	#10 Gauge Zinc-plated Steel
Mounting Style	Stanchion
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Quartz Halogen
Cord Type - Primary	16/3 SOOW
Lamp Type	T-3 RSC
Lamp Wattage - Maximum	500W
Lumens	9200
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	SBG2500



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130110](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION