



Pos	A	B	C	Pos	A	B	C
4	7.00	3.81	5.60	16	22.24	19.05	20.84
6	9.54	6.35	8.14	18	24.78	21.59	23.38
8	12.08	8.89	10.68	20	27.32	24.13	25.92
10	14.62	11.43	13.22	22	29.86	26.67	28.46
12	17.16	13.97	15.76	24	32.40	29.21	31.00
14	19.70	16.51	18.30	26	34.94	31.75	33.54

Specifications:

Current Rating:1.0A AC/DC
Voltage Rating:30V AC/DC
Contact Resistance:20m ohm. Max.
Insulation Resistance:1000M ohm. Min.
Withstanding Voltage:500V AC For One Minute
Operating Temperature Range:-40°C ~ +105°C
Material and Finish
Insulator:High Temp. Plastic (UL94V-0)
Contact:Phosphor Bronze
Finish:Tin Plated
How to Order




TMM-X-X-XX-X

Type
1-IDC Male
2-IDC Plug
3-DIP Male Straight
4-DIP Female Straight
5-DIP Female R/A
6-SMT Female Straight

Packaging
1 - Tape & Reel
2 - Tube
3 - Bag

Number of Positions
04, 06, 08, 10, 12,
14, 16, 18 or 20

Locking System
0-without lock
L-with lock



PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL
X. ±0.3	DESIGN Stephane	2008/04/22	Micro Match SMT Female	Amphenol European Design Center
X.X ±0.1	CHECKED Rob K.	2008/04/23		
X.XX ±0.05	APPROVED Rob K.	2008/04/23		
UNLESS OTHERWISE SPECIFIED	UNIT MM	SIZE A4	DRAWING N° TMM-6-0-XX-X	Scale N.A. Sheet 1 of 1