



General ordering data

Order No.	8019590000
Part designation	DKO 35 24VDC E:U
Version	Optos, 5...48 V DC , 500 mA , Screw connection
EAN	4008190137823
Qty.	10 pc(s).

Dimensions

Clamping range, nom.	4 mm ²
Clamping range, min.	0.5 mm ²
Clamping range, max.	4 mm ²

temperature

Ambient temperature (operational)	-25 °C...+40 °C
Storage temperature	-40 °C...+85 °C

Approvals

Approvals institutes	GOSTME25; CE
----------------------	--------------

Control side

Input frequency, max.	200 Hz
Power rating	145 mW
Rated auxiliary voltage	No
Rated control voltage	24 V DC ±10 %
making voltage	approx. 17 V

General data

Conductor cross-section, flexible, max.	4 mm ²
Solid, max.	4 mm ²
Standards	EN 50178
Humidity	40 °C / 93% rel. humidity, no condensation
Conductor connection system	Screw connection
DIN Rail compatibility	TS 35

Insulation coordination (EN 50 178)

Clearance and creepage distances for control/load ≥ 4 mm side

Overvoltage category	III
Pollution severity	2
Protective separation acc. to VDE 0106	No
Rated impulse withstand voltage	4 kV
Rated voltage	300 V

Load side

Protective circuit	Diode
Pulse duty factor (gen.)	1:2
Rated auxiliary voltage	No
Rated switching current	500 mA
Rated switching voltage	5...48 V DC
Short-circuit-proof	No
Status indicator load side	Green LED
Switch-off delay	Approx. 65 µs
Switch-on delay	Approx. 40 µs
Voltage drop at max. load	≤ 800 mV

Classifications

ETIM20	EC001504
ETIM30	EC001504
eClass 4.1	27-27-09-00
eClass 5.0	27-27-09-90
eClass 5.1	27-27-09-90
eClass 6.0	27-27-09-90

Similar products

Order No.	Part designation	Version
8018630000	DKO 35 5VDC	Optos, 5...48 V DC , 20 mA , Screw connection
8028300000	DKO 35 24VDC 3KHZ E:U	Optos, 5...48 V DC , 20 mA , Screw connection
8248790000	DKO 35 24VDC 3KHZ E:U	Optos, 5...48 V DC , 20 mA , Screw connection
8215630000	DKO 35 24VDC E:O	Optos, 5...48 V DC , 500 mA , Screw connection
8008150000	DKO 35 24VUC	Optos, 5...48 V DC , 20 mA , Screw connection
8215640000	DKO 35 24VDC 3KHZ E:O	Optos, 5...48 V DC , 20 mA , Screw connection
8025910000	DKO 35 48VUC	Optos, 5...48 V DC , 100 mA , Screw connection
8077860000	DKO 35 115VUC	Optos, 5...48 V DC , 50 mA , Screw connection
8008160000	DKO 35 230VUC	Optos, 5...48 V DC , 20 mA , Screw connection