


## Pan head self tapping screws - PoziDriv® - Pointed



DIN 7981 C Z  
BS 4174 AB

### Materials and Finishes

Case hardened steel/Zinc & clear de-embrittled  
Stainless steel/Self colour

### Dimensions

| d          | 2.2  | 2.9  | 3.5  | 3.9 | 4.2  | 4.8   | 5.5   | 6.3   |
|------------|------|------|------|-----|------|-------|-------|-------|
| d          | No.2 | No.4 | No.6 | -   | No.8 | No.10 | No.12 | No.14 |
| D max      | 4.2  | 5.6  | 6.9  | 7.5 | 8.2  | 9.5   | 10.8  | 12.5  |
| H max      | 1.8  | 2.2  | 2.6  | 2.8 | 3.05 | 3.55  | 3.95  | 4.55  |
| Recess No. | 1    | 1    | 2    | 2   | 2    | 2     | 3     | 3     |

### Head Dimensions

|            |      | Thread (d) |       |       |     |       |       |     |     |
|------------|------|------------|-------|-------|-----|-------|-------|-----|-----|
|            |      | 2.2        | 2.9   | 3.5   | 3.9 | 4.2   | 4.8   | 5.5 | 6.3 |
| Length (L) | 4.8  |            | ST    |       |     |       |       |     |     |
|            | 6.4  | ST A2      | ST A2 | ST A2 |     | ST    |       |     |     |
|            | 7.9  | A2         | ST A2 | ST A2 |     | ST    |       |     |     |
|            | 9.5  | ST A2      | ST A2 | ST A2 |     | ST    | ST    |     |     |
|            | 12.7 | ST A2      | ST A2 | ST A2 |     | ST A2 | ST    | ST  | ST  |
|            | 15.9 | ST         | ST A2 | ST A2 |     | ST A2 | ST A2 | ST  | ST  |
|            | 19   |            | ST    | ST A2 |     | ST A2 | ST A2 | ST  | ST  |
|            | 22.2 |            | ST    | ST    |     |       |       |     |     |
|            | 25.4 |            | ST A2 | ST A2 |     | ST A2 | ST A2 | ST  | ST  |
|            | 31.8 |            |       | ST A2 |     | ST A2 | ST A2 | ST  | ST  |
|            | 38   |            |       | ST    |     | ST A2 | ST A2 | ST  | ST  |
|            | 44.5 |            |       |       |     | ST A2 | ST A2 | ST  | ST  |
|            | 50.8 |            |       |       |     | ST A2 | ST A2 | ST  | ST  |
|            | 57   |            |       |       |     | ST    | ST    |     |     |
|            | 63   |            |       |       |     | ST    | ST    | ST  | ST  |

|  |    |  |  |  |  |    |    |    |    |
|--|----|--|--|--|--|----|----|----|----|
|  | 70 |  |  |  |  | ST | ST |    |    |
|  | 75 |  |  |  |  |    | ST | ST | ST |

ST - Steel, Zinc & clear de-embrittled,  
A2 - Stainless steel