


Dimensions: mm (In.)

**Mechanical Specifications:**

- Mechanical Life: 50,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 0.4 Volt-Amps (VA) max. @20V max (AC or DC)
- Contact Resistance: 20mΩmax. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩmin.
- Dielectric Strength: 1,000 V RMS@ sea level

Materials:

- Case & Bushing: Glass filled nylon 66, flame retardant, heat stabilized
- Plunger: Thermoplastic polyester, with internal O-ring seal
- Switch Support: Brass or Steel, electrotin plate
- Contact: Gold plated copper alloy

Note:

- RoHS compliant by exemption

Sealed Sub-Miniature Pushbutton Switch
107-3018-EVX

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[107-3018-EVX](#)