

Relay module; relay with 2 changeover contacts (2u)

Item No.: 286-312



Relay module; relay with 2 changeover contacts (2u)

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	286-312
GTIN / EAN	4045454427986
Content	1
Order amount	1
Customer item number	

Notes

Technical data


Miscellaneous


Color	gray
Pollution degree (1)	2
Rated voltage EN (1) [V]	250 [V]
Rated surge voltage (1) [kV]	4 [kV]
Pull-in time (typ.) [ms]	18 [ms]
Mechanical life	30 x 10 ⁷ switching operations
Drop-out time (typ.) [ms]	3 [ms]
Nominal input current I _N	21.8 mA
Operating power	1,000 mW
Max. switching voltage	250 VAC

Technical data	
Max. switching power (resistive)	1750 VA
Bounce time (typ) [ms]	2 [ms]
Dielectric strength, contact-coil (AC, 1 min) [kVrms</s	4 [kVrms]
Mechanical life at max. load (resistance)	2.5 x 10 ⁵ switching operations
Nominal input voltage VN	24 VDC
Max. continuous current	7 A
Max. make current	0.2 s, 30 A
Pull-in power (mW) [mW]	600 [mW]
Contact material	AgNi 0.15
Weight [g]	39.609 [g]
Width	20 mm / 0.787 in
Standards/specifications	EN 60664-1
Ambient operating temperature at VN	-25 °C ... +40 °C

Images & drawings







Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.