

ELECTRO-ACOUSTIC TRANSDUCER



ROHS COMPLIANT

PART NUMBER:
BRT1207P-01-SEHB

SPECIFICATIONS:

RATED VOLTAGE:	1.5 VDC
OPERATING VOLTAGE:	1 ~ 2
MAX CURRENT:	70 mA
SOUND OUTPUT LEVEL:	75dB @ 10 cm
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2731 Hz
OPERATING TEMPERATURE:	-20 TO +60°C
TONE MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	6.5 ± 1
COIL IMPEDANCE:	22
FRAME DIAMETER:	12.0 mm
FRAME DEPTH:	7.5 mm
MOUNTING DIMENSIONS:	6.5 mm

COMMENTS:

*VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

**VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

DIMENSIONS:

