

DESCRIPTION

The CNX48U, H11BX, MOC8080 and TIL113 have a gallium arsenide infrared emitter optically coupled to a silicon planar photodarlington.



CNX48U	H11B1	H11B2	H11B255	H11B3
MOC8080	TIL113			

FEATURES

- High sensitivity to low input drive current
- Meets or exceeds all JEDEC Registered Specifications
- VDE 0884 approval available as a test option
-add option .300. (e.g., H11B1.300)

APPLICATIONS

- Low power logic circuits
- Telecommunications equipment
- Portable electronics
- Solid state relays
- Interfacing coupling systems of different potentials and impedances.



Parameter	Symbol	Device	Value	Units
TOTAL DEVICE				
Storage Temperature	T _{STG}	All	-55 to +150	°C
Operating Temperature	T _{OPR}	All	-55 to +100	°C
Lead Solder Temperature	T _{SOL}	All	260 for 10 sec	°C
Total Device Power Dissipation @ T _A = 25°C Derate above 25°C	P _D	All	250	mW
			3.3	mW/°C
EMITTER				
Continuous Forward Current	I _F	All	100	mA
Reverse Voltage	V _R	All	6	V
Forward Current - Peak (300 μs, 2% Duty Cycle)	I _{F(pk)}	All	3.0	A
LED Power Dissipation @ T _A = 25°C Derate above 25°C	P _D	All	100	mW
			1.8	mW/°C
DETECTOR				
Collector-Emitter Breakdown Voltage	BV _{CEO}	CNX48U, TIL113	30	V
		H11B1, H11B2 H11B3	25	
		H11B255 MOC8080	55	
Collector-Base Breakdown Voltage	BV _{CBO}	CNX48U, H11B1 H11B2, H11B3 TIL113	30	V
		H11B255 MOC8080	55	V
Emitter-Collector Breakdown Voltage	BV _{ECO}	All	7	V
Detector Power Dissipation @ T _A = 25°C Derate above 25°C	P _D	All	150	mW
			2.0	mW/°C

CNX48U	H11B1	H11B2	H11B255	H11B3
MOC8080	TIL113			

ELECTRICAL CHARACTERISTICS (T_A = 25°C Unless otherwise specified.)

INDIVIDUAL COMPONENT CHARACTERISTICS

Parameter	Test Conditions	Symbol	Device	Min	Typ**	Max	Unit
EMITTER Input Forward Voltage	(I _F = 10 mA)	V _F	H11B1, H11B2 H11B255 MOC8080 TIL113	0.8	1.2	1.5	V
	(I _F = 10 mA)		CNX48U		1.2	1.3	
	(I _F = 10 mA, T _A = -55°C)		MOC8080	0.9	1.3	1.7	
	(I _F = 10 mA, T _A = 100°C)			0.7	1.05	1.4	
	(I _F = 50 mA)		H11B3		1.35	1.5	
Reverse Leakage Current	(V _R = 6 V)	I _R	All		0.001	10	μA
Capacitance	(V _F = 0 V, f = 1.0 MHz)	C	All		50		pF
DETECTOR Collector-Emitter Breakdown Voltage	(I _C = 1 mA, I _F = 0)	BV _{CEO}	CNX48U	30	60		V
	(I _C = 100 μA, I _F = 0)		TIL113				
	(I _C = 10 mA, I _F = 0)		H11B1, H11B2 H11B3	25	60		
	(I _C = 100 μA, I _F = 0)		H11B255	55	70		
	(I _C = 1 mA, I _F = 0)		MOC8080				
Collector-Base Breakdown Voltage	(I _C = 100 μA, I _E = 0)	BV _{CBO}	CNX48U, H11B1 H11B2, H11B3 TIL113	30	100		V
	(I _C = 100 μA, I _F = 0)		H11B255 MOC8080	55	100		
Emitter-Collector Breakdown Voltage	(I _E = 100 μA, I _B = 0)	BV _{ECO}	All	7	10		V
Collector-Emitter Dark Current	(V _{CE} = 10 V, Base Open)	I _{CEO}	All		1	100	nA

Note

** Typical values at T_A = 25°C

CNX48U	H11B1	H11B2	H11B255	H11B3
MOC8080	TIL113			

TRANSFER CHARACTERISTICS (T_A = 25°C Unless otherwise specified.)

DC Characteristics	Test Conditions	Symbol	Device	Min	Typ**	Max	Units
Collector Output Current ⁽¹⁾	(I _F = 10 mA, V _{CE} = 5 V)	I _C (CTR)	MOC8080	50 (500)			mA (%)
			H11B255	10 (100)			
	(I _F = 10 mA, V _{CE} = 1 V)		CNX48U	60 (600)			
			TIL113	30 (300)			
	(I _F = 1 mA, V _{CE} = 5 V)		H11B1	5 (500)			
			H11B2	2 (200)			
			H11B3	1 (100)			
	(I _F = 1 mA, V _{CE} = 1 V)		CNX48U	5 (500)			
	(I _F = 0.5 mA, V _{CE} = 1 V)			1.75 (350)			
Saturation Voltage	(I _F = 1 mA, I _C = 1 mA)	V _{CE(sat)}	H11B1, H11B2 H11B3, MOC8080			1.0	V
	(I _F = 5 mA, I _C = 10 mA)		CNX48U			1.0	
	(I _F = 50 mA, I _C = 50 mA)		H11B255			1.0	
	(I _F = 8 mA, I _C = 2 mA)		TIL113			1.25	
AC Characteristics	(I _C = 10 mA, V _{CE} = 10 V) (R _L = 100 Ω) (Fig.7)	t _{on}	H11B1 H11B2		25		μs
		t _{off}	H11B255 H11B3		18		
	(I _F = 10 mA, V _{CC} = 5 V) (R _E = 100 Ω), (R _{BE} = 1MΩ) (Fig. 8)	t _{on}	CNX48U		3.5		
		t _{off}			36		
	(I _F = 1 mA, V _{CC} = 5 V) (R _E = 1kΩ), (R _{BE} = 10MΩ) (Fig. 8)	t _{on}			70		
		t _{off}			190		
	(I _F = 5 mA, V _{CC} = 10 V) (R _L = 100 Ω) (Fig.7)	t _{on}	MOC8080		3.5		
		t _{off}			25		
	(I _F = 200 mA, I _C = 50 mA) (V _{CC} = 10 V) (R _L = 100 Ω) (Fig.7)	t _{on}	TIL113		0.35	5	
		t _{off}			55	100	

ISOLATION CHARACTERISTICS

Characteristic	Test Conditions	Symbol	Min	Typ**	Max	Units
Input-Output Isolation Voltage ⁽²⁾	(I _{I-O} ≤ 1 μA, V _{rms} , t = 1 min.)		5300			Vac(rms)
Isolation Resistance ⁽²⁾	(V _{I-O} = 500 VDC)	R _{ISO}		10 ¹¹		Ω
Isolation Capacitance ⁽²⁾	(V _{I-O} = ∅, f = 1 MHz)	C _{ISO}		0.8		pf

Note

** Typical values at T_A = 25°C

CNX48U H11B1 H11B2 H11B255 H11B3
MOC8080 TIL113

Fig. 1 Output Current vs. Input Current




Fig. 2 Current Transfer Ratio vs. Ambient Temperature




Fig. 3 Collector Current vs. Collector-Emitter Voltage




Fig. 4 Dark Current vs. Ambient Temperature




Fig. 5 Turn-On Time vs. Input Current





Fig. 6 Turn-Off Time vs. Input Current



CNX48U	H11B1	H11B2	H11B255	H11B3
MOC8080	TIL113			

TYPICAL ELECTRO-OPTICAL CHARACTERISTIC CURVES

(25°C Free air temperature unless otherwise specified) (Cont.)




Fig. 7 Switching Time Test Circuit and Waveforms (All devices except CNX48U)




Fig. 8 Switching Time Test Circuit and Waveforms (CNX48U only)

Notes

1. The current transfer ratio (I_C/I_F) is the ratio of the detector collector current to the LED input current with V_{CE} @ 10 V.
2. For this test, LED pins 1 and 2 are common and phototransistor pins 4,5 and 6 are common.

Package Dimensions (Through Hole)




CNX48U	H11B1	H11B2	H11B255	H11B3
MOC8080	TIL113			

ORDERING INFORMATION

Option	Order Entry Identifier	Description
S	.S	Surface Mount Lead Bend
SD	.SD	Surface Mount; Tape and reel
W	.W	0.4" Lead Spacing
300	.300	VDE 0884
300W	.300W	VDE 0884, 0.4" Lead Spacing
3S	.3S	VDE 0884, Surface Mount
3SD	.3SD	VDE 0884, Surface Mount, Tape & Reel

QT Carrier Tape Specifications ("D" Taping Orientation)



NOTE

All dimensions are millimeters

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.