



Actual

Catalog Number: F8010
Product ID: 7TAI029790R0048
UPC Number: 78621033571
EAN Number: 05415022157888
Status: A

Polypropylene Insulated Twin Ferrule, Length .906 Inches/23.0mm, Pin Length .472 Inches/12mm, Pin Diameter .150 Inches/3.8mm, Base Diameter .339 Inches/8.6mm, Conductor Range 2x12 AWG/2x4.00mm², Color Gray, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: ERG4

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	2x12 AWG
Material	Copper
Color	Gray

European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Construction type	Twin cable end sleeve
Nominal cross section	4mm ²
Insulated	Y
Insulation material	Polypropylene
Colour	Grey
Material	Copper
Surface protection	Tinned
With identification flag	N
Reel packaging	N

Packaging

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	8.6x4.5x4.5
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com