

Amp	Volt	Hz	IP Ident. colour + h	Part No.	Wall mount appliance inlets	3 P + N +	IEC/EN 60 309	 9	EAN No. 4015609...																																	
					external fixing means, 1 top cable entry		<table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>60</td><td>5,3</td><td>80</td><td>74</td><td>73</td><td>31</td><td>117</td><td>16</td></tr><tr><td>32 A</td><td>60</td><td>5,3</td><td>97</td><td>82</td><td>86</td><td>45</td><td>141</td><td>21</td></tr></table>	Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	73	31	117	16	32 A	60	5,3	97	82	86	45	141	21	10/60 177 10 256	000890 023240 023264 023288 000951 024155 024179 024186						
Ampère	b	c	d	e	f	l	n	Pg																																		
16 A	60	5,3	80	74	73	31	117	16																																		
32 A	60	5,3	97	82	86	45	141	21																																		
					internal fixing means, 2 cable entries both, top and bottom (knock-out)		<table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>v</th><th>Pg</th></tr><tr><td>16 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>140</td><td>47,5</td><td>151</td><td>7</td><td>16/21</td></tr><tr><td>32 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>140</td><td>47,5</td><td>160</td><td>7</td><td>16/21</td></tr></table>	Ampère	b	c	d	e	f	l	n	v	Pg	16 A	66,5	5	96	95	140	47,5	151	7	16/21	32 A	66,5	5	96	95	140	47,5	160	7	16/21	5 352 5 399	000920 157884 146154 157877 000982 166992 128556 167005			
Ampère	b	c	d	e	f	l	n	v	Pg																																	
16 A	66,5	5	96	95	140	47,5	151	7	16/21																																	
32 A	66,5	5	96	95	140	47,5	160	7	16/21																																	
					internal fixing means, 2 cable entries both, top and bottom (knock-out)		<table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>u</th><th>v</th><th>Pg</th></tr><tr><td>16 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>140</td><td>47,5</td><td>154</td><td>88</td><td>7</td><td>16/21</td></tr><tr><td>32 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>150</td><td>47,5</td><td>164</td><td>103</td><td>7</td><td>16/21</td></tr></table>	Ampère	b	c	d	e	f	l	n	u	v	Pg	16 A	66,5	5	96	95	140	47,5	154	88	7	16/21	32 A	66,5	5	96	95	150	47,5	164	103	7	16/21	5 357 5 463	000937 165803 023899 165810 000999 167050 024711 024728
Ampère	b	c	d	e	f	l	n	u	v	Pg																																
16 A	66,5	5	96	95	140	47,5	154	88	7	16/21																																
32 A	66,5	5	96	95	150	47,5	164	103	7	16/21																																
					external fixing means, 1 top cable entry		<table><tr><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>n</th><th>u</th><th>Pg</th></tr><tr><td>63 A</td><td>120</td><td>106</td><td>5,6</td><td>152</td><td>118</td><td>118</td><td>232</td><td>113</td><td>29</td></tr></table>	Ampère	a	b	c	d	e	f	n	u	Pg	63 A	120	106	5,6	152	118	118	232	113	29	2 891	001033 024971 024995 025008													
Ampère	a	b	c	d	e	f	n	u	Pg																																	
63 A	120	106	5,6	152	118	118	232	113	29																																	