

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0551244331

Status:

Planned for Obsolescence

Overview:

[minihmc](#)

Description:

HMC™ Rectangular Industrial Terminal 55124, 18 AWG, Blue Retainer

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-54319-001 \(PDF\)](#)

[Product Specification PS-54478-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	55124
Application	Power
Crimp Quality Equipment	Yes
Overview	minihmc
Product Name	HMC™
Physical	
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Silver
Packaging Type	Bag
Wire Insulation Diameter	3.60mm (.142") max.
Wire Size AWG	18
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification	PS-54319-001, PS-54478-001
Sales Drawing	SD-55124-001




image - Reference onlySeries

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

55124Series

Mates With

54296

Use With

55347 housing, 55348 housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for HMC™ 1.60mm (.063") Crimp Terminals	0638231800
Insertion Tool	0638120600
Extraction Tool	0638131800

This document was generated on 02/23/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION