




DUAL-IN-LINE SOCKETS

SERIES 110...605 • AUTOMATIC INSERTION • OPEN FRAME



- High temperature thermoplastic insulator with standoffs is compatible with standard automatic insertion equipment and all soldering processes
- Soft copper alloy machined pins allow clinching. Chamfered contact entry allows for ease of IC insertion without bent leads
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 110 uses MM #1005 pins. See page 166 for details
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION						
	A	B	C								
6	0.3	0.3	0.4	67	110-XX-306-41-605000						
8	0.4	0.3	0.4	50	110-XX-308-41-605000						
14	0.7	0.3	0.4	28	110-XX-314-41-605000						
16	0.8	0.3	0.4	25	110-XX-316-41-605000						
18	0.9	0.3	0.4	22	110-XX-318-41-605000						
20	1.0	0.3	0.4	20	110-XX-320-41-605000						
24	1.2	0.3	0.4	16	110-XX-324-41-605000						
22	1.1	0.4	0.5	18	110-XX-422-41-605000						
24	1.2	0.6	0.7	16	110-XX-624-41-605000						
28	1.4	0.6	0.7	14	110-XX-628-41-605000						
32	1.6	0.6	0.7	12	110-XX-632-41-605000						
40	2.0	0.6	0.7	10	110-XX-640-41-605000						
XX=Plating Code See Below					RoHS-2 2011/65/EU						
SPECIFY PLATING CODE XX =						91	93		41 ◆	43 ◆	47 ◆
Sleeve (Pin) 						200 μ" Sn/Pb	200 μ" Sn/Pb		200 μ" Sn	200 μ" Sn	200 μ" Sn
Contact (Clip) 						10 μ" Au	30 μ" Au		10 μ" Au	30 μ" Au	Au Flash

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[110-43-640-41-605000](#) [110-43-632-41-605000](#) [110-43-628-41-605000](#) [110-43-624-41-605000](#) [110-43-422-41-605000](#) [110-43-324-41-605000](#) [110-43-320-41-605000](#) [110-43-318-41-605000](#) [110-43-316-41-605000](#) [110-43-314-41-605000](#) [110-43-308-41-605000](#) [110-43-306-41-605000](#) [110-93-308-41-605000](#) [110-93-640-41-605000](#) [110-93-632-41-605000](#) [110-93-628-41-605000](#) [110-93-624-41-605000](#) [110-93-422-41-605000](#) [110-93-324-41-605000](#) [110-93-320-41-605000](#) [110-93-318-41-605000](#) [110-93-316-41-605000](#) [110-93-314-41-605000](#) [110-93-306-41-605000](#)