



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MINIMUM BUNDLE DIAMETER	MAXIMUM BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH = "L" ±.3 [7]	
MLT2.7WLH-LP316	2.0" [51]	2.7" [69]	50	10.2" [259]	(A)
MLT4WLH-LP316	2.0" [51]	4.0" [102]	50	14.3" [362]	(A)
MLT6WLH-LP316	2.0" [51]	6.0" [152]	50	20.5" [521]	(A)
MLT8WLH-LP316	2.0" [51]	8.0" [203]	50	26.8" [679]	(B)



TITLE		WAVE-TY LIGHT-HEAVY	
ITEM REVISION NAME		CUSTOMER DRAWING	
N41138BS/05		PANDUIT	
DATASET FILE NAME		N41138BS/05	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54] .xxx ± .005 [.127]		316 STAINLESS STEEL	
.xx ± .01 [.25] ANGLES ± 5 °		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		N41138BS_DC	
DRAWN BY	DATE	CHK	SCALE
JAMB	03/03	DPN	2:1
SHT 1 OF 1		A	