

| LOC | DIST | REVISIONS |     |                        |            |          |
|-----|------|-----------|-----|------------------------|------------|----------|
|     |      | P         | LTR | DESCRIPTION            | DATE       | DWN APVD |
|     |      | O         |     | RELEASED(FJ00-1409-97) | 07OCT97    | S.H H.K  |
|     |      | A         |     | REVISED(FJ00-1740-98)  | 24SEP98    | S.H Y.Y  |
|     |      | B         |     | REVISED(FJ00-1195-00)  | 17 JUL '00 | S.H      |

## NOTE

## ① MATERIAL

(1) HOUSING : LCP(UL94V-0, BLACK)

(2) CONTACT : PHOSPHOR BRONZE

FINISH : CONTACT AREA ; Au PL. OVER 0.001 MIN. Ni PL.





SOLDERING AREA : 0.001 MIN. TIN-LEAD OVER 0.001 MIN. Ni PL.

(3) G-CONT. WITH RETENTION-LEG : BRASS

FINISH : 0.001 MIN. TIN-LEAD PL. OVER 0.001 MIN. Ni PL.

## ② INDICATE DATE CODE.

③ THIS DIM. IS 1.6±0.08 WHEN THE CONTACT PUSH TO HOUSING.



## 注記

## ① 材料

(1)ハウジング : LCP (UL94V-0, 黒色)

(2)コンタクト : 焼青銅 仕上げ : ニッケル下地めっき0.001以上

接触部 : 金めっき

タイン部 : 半田めっき0.001以上

(3)リテンションレグ付グランドコンタクト : 黄銅


仕上げ : ニッケル下地めっき0.001以上, 半田めっき0.001以上

## ② デートコード表示

③ ハウジングに押さえつけたときの寸法は1.6±0.08とする。

|             |            |     |    |      |       |      |       |       |      |        |        |      |      |
|-------------|------------|-----|----|------|-------|------|-------|-------|------|--------|--------|------|------|
| 1123283-9   | 0.0002     | 80  | 79 | 54.2 | 57.87 | 66.5 | 55.27 | 49.53 | 66.4 | 50.165 | 58.765 | 62.0 | 64.7 |
| 5-1123283-5 | 0.00076    | 40  | 39 | 28.8 | 32.47 | 41.1 | 29.87 | 24.13 | 41.0 | 24.765 | 33.365 | 36.6 | 39.3 |
| 1123283-5   | 0.0002     | 40  | 39 | 28.8 | 32.47 | 41.1 | 29.87 | 24.13 | 41.0 | 24.765 | 33.365 | 36.6 | 39.3 |
| PART NO.    | Au PL. THK | POS | n  | A    | B     | C    | D     | E     | F    | G      | H      | J    | K    |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
単位 : 概  
MMMATERIAL  
材料TOLERANCES UNLESS  
OTHERWISE SPECIFIED:  
一般公差

0-PLC ±0.2:10=<  
1-PLC ±0.25:10>,30=<  
2-PLC ±0.3:30>  
3-PLC ±  
4-PLC ±  
ANGLES ±3°

FINISH  
仕上

DWN 07/OCT/'97

S.HASHIMOTO

CHK 07/OCT/'97

H.KODAMA

APVD 07/OCT/'97

H.KODAMA

PRODUCT SPEC  
製品規格 108-5290APPLICATION SPEC  
取付適用規格

WEIGHT -

CUSTOMER DRAWING

WIRE RANGE  
包合電線断面積INSULATION DIA  
被覆外径

AMP

Tyco Electronics AMP K.K.

Kawasaki, Japan

NAME  
名称PLUG ASS'Y SMT TYPE, CHAMP.050(I)  
BLINDMATE WITH G-CONT.(P.C.B t=0.8mm)

SIZE

CAGE CODE

DRAWING NO  
番号

A3 00779 C-1123283

RESTRICTED TO

SCALE  
尺度 -SHEET  
1 OF 2REV  
B

