

Technical Data

Nitrile grade cord to BS 2751. BA 70. DTD 458 A—Grade A.

Cord Diameters

Uncompressed	Compressed
1.8mm ± 0.20mm	1/16" (1.6mm)
2.6mm ± 0.25mm	3/32" (2.4mm)
3.5mm ± 0.25mm	1/8" (3.2mm)
5.3mm ± 0.35mm	3/16" (4.8mm)
7.0mm ± 0.40mm	1/4" (6.4mm)
8.7mm ± 0.40mm	5/16" (7.9mm)
10.4mm ± 0.50mm	3/8" (9.5mm)

Cord tolerances to BS 3734/ISO 3302.



The Loctite 'O' Ring Kit

O RING KIT & SPARES

'O' Ring Kit - 1 Bottle IDH No 480166
'O' Ring Kit - 2 Bottles IDH No 229234

	IDH No	Description
KIT	480166	O' RING KIT 1 BOTTLE OF LOCTITE 406
KIT	229234	O' RING KIT 2 BOTTLES OF LOCTITE 406
SPARE CORD	142628	O'RING CORD 1.6mm (1/16") x 8.5m length
SPARE CORD	235568	O'RING CORD 4.8mm (3/16") x 8.5m Length
SPARE CORD	142629	O'RING CORD 2.4mm (3/32") x 8.5m length
SPARE CORD	235567	O'RING CORD 3.2mm (1/8") x 8.5m length
SPARE CORD	235569	O'RING CORD 6.4mm (1/4") x 8.5m length
SPARE CORD	142632	O'RING CORD 8.4mm (5/16") x 8.5m length

Nato Stock Numbers:

Kit: HI-5330 99 978 4778
406 x 20g: HI-8040 99 729 3250

LOCTITE