









Amp	Volt	Hz	IP	Ident. colour + h	Part No.	Plugs and sockets for extra-low voltages up to 50 V	3 pole	IEC/EN 60 308	9	EAN 4013603...																										
IP44 16 24~ 50/60 10 150 42~ 50/60 12 10 151 42~ 100/200 4 10 152 42~ 300 2 10 153 42~ 400 3 10 154 42~ >400/500 11 10 155 32 24~ 50/60 11 150 42~ 50/60 12 11 151 42~ 100/200 4 11 152 42~ 300 2 11 153 42~ 400 3 11 154 42~ >400/500 11 11 155						wall socket outlets, external fixing means. 1 top cable entry    <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>54,5</td><td>5,2</td><td>81</td><td>70</td><td>72</td><td>28</td><td>119</td><td>21</td></tr><tr><td>32 A</td><td>54,5</td><td>5,2</td><td>81</td><td>70</td><td>72</td><td>28</td><td>119</td><td>21</td></tr></table>		Ampère	b	c	d	e	f	l	n	Pg	16 A	54,5	5,2	81	70	72	28	119	21	32 A	54,5	5,2	81	70	72	28	119	21	10	003938 003945 003952 003969 003976 003953
Ampère	b	c	d	e	f	l	n	Pg																												
16 A	54,5	5,2	81	70	72	28	119	21																												
32 A	54,5	5,2	81	70	72	28	119	21																												
IP44 16 24~ 50/60 10 140 42~ 50/60 12 10 141 42~ 100/200 4 10 142 42~ 300 2 10 143 42~ 400 3 10 144 42~ >400/500 11 10 145 32 24~ 50/60 11 140 42~ 50/60 12 11 141 42~ 100/200 4 11 142 42~ 300 2 11 143 42~ 400 3 11 144 42~ >400/500 11 11 145						wall socket outlets, external fixing means, cable entries: top: 1 x Pg 21, bottom: 2 x Pg 16    <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th></tr><tr><td>16 A</td><td>80</td><td>6,2</td><td>83</td><td>90</td><td>83</td><td>60</td><td>125</td></tr><tr><td>32 A</td><td>80</td><td>6,2</td><td>83</td><td>90</td><td>83</td><td>60</td><td>125</td></tr></table>		Ampère	b	c	d	e	f	l	n	16 A	80	6,2	83	90	83	60	125	32 A	80	6,2	83	90	83	60	125	10	003877 003884 003891 003907 003914 003921			
Ampère	b	c	d	e	f	l	n																													
16 A	80	6,2	83	90	83	60	125																													
32 A	80	6,2	83	90	83	60	125																													
IP44 16 24~ 50/60 10 290 42~ 50/60 12 10 291 42~ 100/200 4 10 292 42~ 300 2 10 293 42~ 400 3 10 294 42~ >400/500 11 10 295 32 24~ 50/60 11 290 42~ 50/60 12 11 291 42~ 100/200 4 11 292 42~ 300 2 11 293 42~ 400 3 11 294 42~ >400/500 11 11 295						plugs, flexible cable entry    <table><tr><th>Ampère</th><th>d</th><th>e</th><th>f</th><th>m</th><th>n</th><th>Øp</th></tr><tr><td>16 A</td><td>135</td><td>59</td><td>55</td><td>99</td><td>22,5</td><td>8/21</td></tr><tr><td>32 A</td><td>135</td><td>59</td><td>55</td><td>99</td><td>22,5</td><td>8/21</td></tr></table>		Ampère	d	e	f	m	n	Øp	16 A	135	59	55	99	22,5	8/21	32 A	135	59	55	99	22,5	8/21	10	004447 004454 004461 004476 004485 004492						
Ampère	d	e	f	m	n	Øp																														
16 A	135	59	55	99	22,5	8/21																														
32 A	135	59	55	99	22,5	8/21																														
IP44 16 24~ 50/60 10 250 42~ 50/60 12 10 251 42~ 100/200 4 10 252 42~ 300 2 10 253 42~ 400 3 10 254 42~ >400/500 11 10 255 32 24~ 50/60 11 250 42~ 50/60 12 11 251 42~ 100/200 4 11 252 42~ 300 2 11 253 42~ 400 3 11 254 42~ >400/500 11 11 255						plugs, gland entry Pg 16    <table><tr><th>Ampère</th><th>d</th><th>e</th><th>f</th><th>m</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>128</td><td>59</td><td>55</td><td>99</td><td>22,5</td><td>16</td></tr><tr><td>32 A</td><td>128</td><td>59</td><td>55</td><td>99</td><td>22,5</td><td>16</td></tr></table>		Ampère	d	e	f	m	n	Pg	16 A	128	59	55	99	22,5	16	32 A	128	59	55	99	22,5	16	10	004255 004260 004270 004287 004294 004300						
Ampère	d	e	f	m	n	Pg																														
16 A	128	59	55	99	22,5	16																														
32 A	128	59	55	99	22,5	16																														

Other frequencies and voltages up to 50 V on request