

Part Number: 5530199F

General Description	
Series	553
Description	3 mm White/White Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Untinted, Non -Diffused
Viewing Angle	45
LED Centerline	5.0mm
Absolute Maximum Ratings (Ta = 25Â°)	
Derating	0.42 (mA/degC)
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-40 to +85
Storage Temperature	-40 to +100
Operating Characteristics	
Color	White
LED Type	High Efficiency
LED Position	1,2
Luminous Intensity Min	950
Forward Voltage Typical	3.2
Forward Voltage Max	3.7
Test Current mA	20mA



5530199F

check stock



This is a
RoHS Compliant Product.
To learn more click here